

NCH75R190S



N-Channel Silicon Carbide MOSFET

|                           |                             |                        |
|---------------------------|-----------------------------|------------------------|
| <b>Voltage:</b> 750 Volts | <b>Current:</b> 15.5 Ampers | <b>Package:</b> TO-252 |
|---------------------------|-----------------------------|------------------------|

**Features**

- NH'S Advanced Silicon Carbide MOSFET Technology
- High Blocking Voltage And Low Capacitances
- High-Speed Switching For Very Low Switching Losses
- Excellent Qg\*Rds(on) Product(FOM)


**Typical Applications**

- High Voltage DC/DC Converters
- Adaptor And Charger
- Battery Chargers And Motor Drives
- LED Drives And LED Lighting


**Product Summary**

|                                       |      |    |
|---------------------------------------|------|----|
| V <sub>DS</sub> Min.@T <sub>j</sub>   | 750  | V  |
| I <sub>D</sub> Min.@Ta                | 15.5 | A  |
| RDS(ON)(TYP)@18V,T <sub>j</sub> =25°C | 190  | mΩ |

**Diagram:**



**Polarity:**



**\*100% UIS TESTED**

**\*100% ΔVDS TESTED**

**Absolute Maximum Ratings (Ta=25°C Unless Otherwise Specified)**

| Parameter  | Test Conditions   | Symbol               | Ratings     | Unit |
|--|---|----------------------|-------------|------|
| Drain-Source Voltage   |   | V <sub>DS</sub>      | 750         | V    |
| Gate-Source Voltage  |   | V <sub>GS</sub> MAX. | -10/+22     | V    |
|  |   | V <sub>GS</sub> O.P. | 0/+15 or 18 |      |
| Continuous Drain Current (Note 1)  | Ta= 25 °C   | I <sub>D</sub>       | 15.5        | A    |
|  | Ta= 100 °C  |                      | 12.4        |      |
| Drain Current-Pulse (Note 1)   | T <sub>j</sub> < 175 °C   | I <sub>DM</sub>      | 27          | A    |
| Maximum Power Dissipation Power  | Ta= 25 °C   | P <sub>D</sub>       | 71          | W    |
| Dissipation Derating Factor Above 25°C                                       | Ta= 100 °C  |                      | 36          |      |
| Derating Factor  |   | D <sub>F</sub>       | 0.48        | W/°C |
| Avalanche Current,Single Pulse (Note 1)                                      | L= 0.5 mH   | I <sub>AS</sub>      | 10.0        | A    |
| Single Pulse Avalanche Energy (Note 1)<br>Test Circuit & Waveform See Fig.22 | L= 0.5 mH<br>IAS= 10.0 A, RG= 10.0 Ω<br>Starting T <sub>j</sub> =25 °C, VG = 18.0 V | E <sub>AS</sub>      | 25          | mJ   |

**Thermal Characteristics (Ta=25°C Unless Otherwise Specified)**

| Parameter   | Test Conditions  | Symbol           | Typ.       | Unit |
|---|--|------------------|------------|------|
| Junction Temperature  |  | T <sub>J</sub>   | -55 to 175 | °C   |
| Storage Temperature Range                                   |  | T <sub>STD</sub> | -55 to 175 | °C   |
| Thermal Resistance Junction To Ambient<br>With Steady-State | Still Air Environment<br>With Ta=25°C                  | R <sub>θJA</sub> | 50         | °C/W |
| Thermal Resistance Junction-Case<br>With Steady-State       | Device Mounted On<br>1 in2 FR-4 Board With 2oz. Copper | R <sub>θJC</sub> | 2.1        |      |

Notes: 1.Pulse Width Limited By Max. Junction Temperature. (See Fig. 19).

**NCH75R190S**
**N-Channel Silicon Carbide MOSFET**

**Electrical Characteristics (Ta=25°C Unless Otherwise Specified )**

| Parameter   | Test Conditions                  | Symbol              | Min.                | Typ. | Max. | Unit |    |
|---|----------------------------------|---------------------|---------------------|------|------|------|----|
| <b>Static Off Characteristics</b>                                   |                                  |                     |                     |      |      |      |    |
| Drain-Source Breakdown Voltage                                      | VGS=0V, ID=100uA                 | BV <sub>DSS</sub>   | 750                 | --   | --   | V    |    |
| Zero Gate Voltage Drain Current                                     | VDS= 0 V, VGS=0V, Tj=25°C        | I <sub>DSS</sub>    | --                  | 0.1  | 20   | uA   |    |
|   | VDS= 750 V, VGS=0V, Tj=175°C     |                     | --                  | 3    | --   |      |    |
| Gate To Source Leakage Current                                      | VGS= 22 V, VDS=0V                | I <sub>GSS</sub>    | --                  | --   | 250  | nA   |    |
| Source To Gate Leakage Current                                      | VGS= -10 V, VDS=0V               | I <sub>SGS</sub>    | --                  | --   | 250  | nA   |    |
| Forward Transconductance  | ID= 4.7 A, VDS= 20 V             | g <sub>fs</sub>     | --                  | 3.6  | --   | S    |    |
| <b>Static On Characteristics</b>                                    |                                  |                     |                     |      |      |      |    |
| Gate Threshold Voltage  | VGS= VDS, ID=10mA, Tj=25°C       | V <sub>GS(TH)</sub> | 3                   | 4.1  | 5    | V    |    |
|   | VGS= VDS, ID=10mA, Tj=175°C      |                     | --                  | 3.0  | --   |      |    |
| Drain-Source On Resistance  | ID= 4.7 A, VGS= 18.0 V, Tj=25°C  | R <sub>DS(ON)</sub> | --                  | 190  | 240  | mΩ   |    |
|   | ID= 4.7 A, VGS= 18.0 V, Tj=175°C |                     | --                  | 209  | 264  |      |    |
|   | ID= 4.7 A, VGS= 15.0 V, Tj=25°C  |                     | --                  | 247  | 360  |      |    |
|   | ID= 4.7 A, VGS= 15.0 V, Tj=175°C |                     | --                  | 220  | 320  |      |    |
| <b>Dynamic Characteristics</b>                                      |                                  |                     |                     |      |      |      |    |
| Input Capacitance   | VDS= 650 V                       | C <sub>iss</sub>    | --                  | 294  | --   | pF   |    |
| Output Capacitance  | VGS= 0 V                         | C <sub>oss</sub>    | --                  | 25   | --   | pF   |    |
| Reverse Transfer Capacitance  | F= 1 MHz                         | C <sub>rss</sub>    | --                  | 4    | --   | pF   |    |
| Gate Resistance   | VGS=0V, VDS=0V, Freq.=1MHz       | R <sub>g</sub>      | --                  | 25   | --   | Ω    |    |
| <b>Switching Paramters (Test Circuit &amp; Waveform See Fig.20)</b> |                                  |                     |                     |      |      |      |    |
| Turn-On Delay Time  | VDS= 400 V<br>ID= 4.7 A          | Tj=25°C             | t <sub>d(on)</sub>  | --   | 13   | --   | ns |
|   |                                  | Tj=175°C            | --                  | 12.4 | --   |      |    |
| Turn-On Rise Time   | VGS= 0/+18 V<br>RG= 10.0 Ω       | Tj=25°C             | t <sub>r</sub>      | --   | 8.5  | --   | ns |
|   |                                  | Tj=175°C            | --                  | 8.1  | --   |      |    |
| Turn-Off Delay Time   | L= 600 μH                        | Tj=25°C             | t <sub>d(off)</sub> | --   | 10   | --   | ns |
|   |                                  | Tj=175°C            | --                  | 9.5  | --   |      |    |
| Turn-Off Rise Time  |                                  | Tj=25°C             | t <sub>f</sub>      | --   | 6    | --   | ns |
|   |                                  | Tj=175°C            | --                  | 5.1  | --   |      |    |
| Turn-On Switching Loss  |                                  | Tj=25°C             | E <sub>on</sub>     | --   | 20.0 | --   | μJ |
|   |                                  | Tj=175°C            | --                  | 19.0 | --   |      |    |
| Turn-Off Switching Loss   |                                  | Tj=25°C             | E <sub>off</sub>    | --   | 14.9 | --   | μJ |
|   |                                  | Tj=175°C            | --                  | 13.6 | --   |      |    |
| Total Switching Energy  |                                  | Tj=25°C             | E <sub>tot</sub>    | --   | 34.9 | --   | μJ |
|   |                                  | Tj=175°C            | --                  | 32.6 | --   |      |    |

NCH75R190S

N-Channel Silicon Carbide MOSFET



Electrical Characteristics (Ta=25°C Unless Otherwise Specified )







| Parameter  | Test Conditions                 | Symbol           | Min.     | Typ. | Max. | Unit |    |
|--|---------------------------------|------------------|----------|------|------|------|----|
| <b>Gate Charge Paramters (Test Circuit &amp; Waveform See Fig.21)</b>                                  |                                 |                  |          |      |      |      |    |
| Total Gate Charge  | VDS= 400 V                      | Q <sub>g</sub>   | --       | 12   | --   | nC   |    |
| Gate-Source Charge   | VGS= 0/+18 V                    | Q <sub>gs</sub>  | --       | 4    | --   | nC   |    |
| Gate-Drain Charge  | ID= 4.7 A                       | Q <sub>gd</sub>  | --       | 1.5  | --   | nC   |    |
| <b>Drain-Source Diode Characteristics And Maximum Ratings (Test Circuit &amp; Waveform See Fig.23)</b> |                                 |                  |          |      |      |      |    |
| Max. Diode Forward Cuurent   | Tj= 25 °C                       | I <sub>s</sub>   | --       | --   | 15.5 | A    |    |
| tp Limited by Tj(max)  | Tj= 100 °C                      |                  | --       | --   | 12.4 |      |    |
| Max. Pulsed Forward Cuurent  |                                 | I <sub>SM</sub>  | --       | --   | 23   | A    |    |
| Diode Forward Voltage  | ID= 2.8 A, VGS=-0V              | V <sub>SD</sub>  | Tj=25°C  | --   | 3.3  | --   | V  |
|  |                                 |                  | Tj=175°C | --   | 2.8  | --   |    |
| Reverse Recovery Time  | IS= 7.8 A<br>di/dt= 1000.0 A/us | t <sub>rr</sub>  | Tj=25°C  | --   | 9.8  | --   | ns |
|  |                                 |                  | Tj=175°C | --   | 11.1 | --   |    |
| Reverse Recovery Charge  | VGS= 0.0 V<br>VDS= 400 V        | Q <sub>rr</sub>  | Tj=25°C  | --   | 32   | --   | nC |
|  |                                 |                  | Tj=175°C | --   | 36.8 | --   |    |
| Reverse Recovery Current   |                                 | I <sub>rrm</sub> | Tj=25°C  | --   | 7.0  | --   | A  |
|  |                                 |                  | Tj=175°C | --   | 6.6  | --   |    |
| Reverse Recovery Energy  |                                 | E <sub>rr</sub>  | Tj=25°C  | --   | 13.7 | --   | μJ |
|  |                                 |                  | Tj=175°C | --   | 14.6 | --   |    |

NCH75R190S

N-Channel Silicon Carbide MOSFET



Typical Characteristics Curves



NCH75R190S

N-Channel Silicon Carbide MOSFET



Typical Characteristics Curves




Fig.7-Gate Source Threshold Voltage Vs. Junction Temperature




Fig.8-Transfer Characteristics




Fig.9-Typical Switching Energy Vs. Junction Temperature




Fig.10-Typical Switching Energy Vs. External Gate Resistance




Fig.11-Typical Switching Energy Vs. Drain Source Current




Fig.12-Typical Switching Energy Vs. Drain Source Voltage

NCH75R190S

N-Channel Silicon Carbide MOSFET



Typical Characteristics Curves




Fig.13-Maximum Continuous Drain Current Vs. Case Temperature




Fig.14-Maximum Power Dissipation Vs. Case Temperature




Fig.15-Source-To-Drain Diode Forward Voltage




Fig.16-Gate Charge Waveform




Fig.17-Typical Capacitance Vs. Drain-To-Source Voltage




Fig.18-Maximum Safe Operating Area(SOA)

NCH75R190S

N-Channel Silicon Carbide MOSFET



Typical Characteristics Curves




Fig.19- Normalized Maximum Transient Thermal Impedance Vs.Pulse Width

Test Circuit & Waveform




Fig.20- Inductive Switching Test Circuit & Waveform

NCH75R190S

N-Channel Silicon Carbide MOSFET



Test Circuit & Waveform




Fig.21-Gate Charge Test Circuit & Waveform




Fig.22- Unclamped Inductive Switching (UIS) Test Circuit & Waveform





Fig.23- Diode Recovery Test Circuit & Waveform

NCH75R190S

N-Channel Silicon Carbide MOSFET




OUTLINE DRAWINGS



TO-252

| OUTLINE DIMENSIONS |             |      |       |        |      |        |
|--------------------|-------------|------|-------|--------|------|--------|
| Dim.               | Millimeters |      |       | Inches |      |        |
|                    | Min.        | Typ. | Max.  | Min.   | Typ. | Max.   |
| A                  | 6.10        | -    | 7.10  | 0.2402 | -    | 0.2795 |
| B                  | 4.80        | -    | 5.80  | 0.1890 | -    | 0.2283 |
| C                  | 1.95        | -    | 2.55  | 0.0768 | -    | 0.1004 |
| D                  | 0.35        | -    | 0.75  | 0.0138 | -    | 0.0295 |
| E                  | 9.25        | -    | 10.75 | 0.3642 | -    | 0.4232 |
| F                  | 5.60        | -    | 6.60  | 0.2205 | -    | 0.2598 |
| G                  | 2.50        | -    | 3.10  | 0.0984 | -    | 0.1220 |
| H                  | 0.65        | -    | 1.05  | 0.0256 | -    | 0.0413 |
| J                  | 2.10        | -    | 2.50  | 0.0827 | -    | 0.0984 |
| L                  | 1.00        | -    | 1.40  | 0.0394 | -    | 0.0551 |
| M                  | 0.35        | -    | 0.75  | 0.0138 | -    | 0.0295 |

RECOMMENDED LAYOUT DRAWINGS



TO-252

| OUTLINE DIMENSIONS |             |      |      |        |        |      |
|--------------------|-------------|------|------|--------|--------|------|
| Dim.               | Millimeters |      |      | Inches |        |      |
|                    | Min.        | Typ. | Max. | Min.   | Typ.   | Max. |
| A                  | -           | 6.09 | -    | -      | 0.2398 | -    |
| B                  | -           | 7.57 | -    | -      | 0.2980 | -    |
| C                  | -           | 6.64 | -    | -      | 0.2614 | -    |
| D                  | -           | 2.30 | -    | -      | 0.0906 | -    |
| E                  | -           | 2.76 | -    | -      | 0.1087 | -    |
| F                  | -           | 1.42 | -    | -      | 0.0559 | -    |

NCH75R190S

N-Channel Silicon Carbide MOSFET





MARKING INFORMATION



MARKING INSTRUCTIONS

NH=Nihang Trademark  
 FF=Product Line Code,According To Actual Changes  
 YWW=Date Code,According To Actual Changes  
 LLWWF=Inernal Code,According To Actual Changes  
 NCH75R190S=Model

PACKAGING



TO-252

| OUTLINE DIMENSIONS |            |      |        |        |      |        |
|--------------------|------------|------|--------|--------|------|--------|
| Dim.               | Milimeters |      |        | Inches |      |        |
|                    | Min.       | Typ. | Max.   | Min.   | Typ. | Max.   |
| <b>TAPE</b>        |            |      |        |        |      |        |
| A                  | 2.60       | -    | 2.80   | 0.1024 | -    | 0.1102 |
| C                  | 15.60      | -    | 16.40  | 0.6142 | -    | 0.6457 |
| D                  | 7.70       | -    | 8.30   | 0.3031 | -    | 0.3268 |
| E                  | 7.30       | -    | 7.70   | 0.2874 | -    | 0.3031 |
| F                  | 10.20      | -    | 10.80  | 0.4016 | -    | 0.4252 |
| G                  | 6.70       | -    | 7.10   | 0.2638 | -    | 0.2795 |
| Q Φ                | 1.40       | -    | 1.60   | 0.0551 | -    | 0.0630 |
| <b>REEL</b>        |            |      |        |        |      |        |
| L                  | 328.00     | -    | 332.00 | 12.913 | -    | 13.071 |
| R                  | 12.00      | -    | 14.00  | 0.4724 | -    | 0.5512 |
| M                  | 19.40      | -    | 23.40  | 0.7638 | -    | 0.9213 |

PACKING INFORMATION

| Package Type | Package Code | Product Weight Approx(g/Pcs) | Package Method | Quantity (Pcs/Min. Pack.) | Quantity (Pcs/Inner Box) | Quantity (Pcs/Carton) |
|--------------|--------------|------------------------------|----------------|---------------------------|--------------------------|-----------------------|
| TO-252       | P1           | 0.321                        | 13" Reel       | 2500                      | 5000                     | 30000                 |
| TO-252       | P2           | 0.321                        | 13" Reel       | 2500                      | 2500                     | 25000                 |

**NCH75R190S**


**N-Channel Silicon Carbide MOSFET**



**Recommended wave soldering condition**

|                 |                  |                 |
|-----------------|------------------|-----------------|
| Product         | Peak Temperature | Soldering Time  |
| Pb-free devices | 260 +0/-5 °C     | 5 +1/-1 seconds |

**Recommended temperature profile for IR reflow**



Note : All temperatures refer to topside of the package, measured on the package body surface.

**Disclaimer**

- Reproducing and modifying information of the document is prohibited without permission from Nihang Electronics Technology Co., LTD
- Nihang Electronics Technology Co., LTD. reserves the rights to make changes of the content herein the document anytime without notification.
- Nihang Electronics Technology Co., LTD. disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- Nihang Electronics Technology Co., LTD. does not assume any and all implied warranties,including warranties of fitness for particular purpose,non-infringement and merchantability.
- Applications shown on the herein document are examples of standard use and operation.Customers are responsible in comprehending the suitable use in particular applications.Nihang Electronics Technology Co., LTD.makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.
- The products shown herein are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining,such as medical instruments.transportation equipment,aerospae machinery et cetera.Customers usin or selling these products for use in such applications do so at their own rish and agree to fully indemnify Nihang Electronics Technology Co., LTD.for any damages resulting resulting from such improper use or sale.
- When the appearance of the product and chip size does not change, in order to product the customer. quality, change the internal structure and the production process Nihang can not notify

**NCH75R190S**

**N-Channel Silicon Carbide MOSFET**



**Specification Revision History**

| Rev. | Date       | Changed Items | Pre-Changed Content | Changed Content |
|------|------------|---------------|---------------------|-----------------|
| A/1  | 2025-10-20 | First Issue   |                     |                 |
|      |            | Blank Below   |                     |                 |