

BT152

SCR

GENERAL DESCRIPTION

The BT152 is a thyristor, it uses our advanced technology to provide customers with high bidirectional blocking voltage capability and high thermal cycling performance, etc.

The BT152 is suitable for motor control, industrial, static switching, heating and domestic lighting, etc.

FEATURES

- * High bidirectional blocking voltage capability
- * High thermal cycling performance

MARKING




BT152=Device Code

800E:VDRM/VRRM=800V

XXXX=Date Code

Solid Dot=Green molding compound



Pin1:K (Cathode)

Pin2:A (Anode)

Pin3:G (Gate)

ABSOLUTE MAXIMUM RATINGS (TC=25°C, unless otherwise specified)

SYMBOL	PARAMETER		TEST CONDITION	VALUE	UNIT
V _{DRM}	Repetitive Peak off-state voltage	BT152-4	T _J =25℃	450	V
		BT152-6		650	
		BT152-8		800	
I _{T(AV)}	Average On-State Current（half sine wave;T _c ≤103℃）			13	A
I _{T(RMS)}	RMS On-State Current（All Conduction Angles）			20	A
I _{TSM}	Non-repetitive peak on-state current (half sine wave;T _J =25℃ prior to surge)		t=10ms	200	A
			t=8.3ms	220	
I ² t	I ² t for fusing		t=10ms	200	A ² S
di/dt	Critical rate of rise of on-state current		I _{TM} = 50A; I _g =0.2A; di _g /dt =0.2A/μs	200	A/μs
I _{GM}	Peak gate current			5	A
V _{GM}	Peak gate voltage			5	V
V _{RGM}	Peak Reverse Gate Voltage			5	V
P _{GM}	Peak gate Power			20	W
P _{G(AV)}	Average gate Power Dissipation (over any 20ms period)		T _J =125℃	0.5	W
T _J	Operating Junction Temperature			125	℃
T _{stg}	Storage Temperature			-40 to +150	℃

Notes: Absolute maximum ratings are those values beyond which the device could be permanently damaged.

Absolute maximum ratings are stress ratings only and functional device operation is not implied.

BT152

SCR

■ THERMAL RESISTANCES

PARAMETER		SYMBOL	RATINGS	UNIT
Junction to Ambient	TO-220F	R θ JA	60	K/W
	TO-252		75	
Junction to Case	TO-220F	R θ JC	1.1	K/W
	TO-252		2.3	

■ ELECTRICAL CHARACTERISTICS (T_J=25°C, unless otherwise specified)

PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
STATIC CHARACTERISTICS						
Gate trigger current	I _{GT}	V _D =12V;I _T =0.1A		3	32	mA
Latching current	I _L	V _D =12V;I _{GT} =0.1A		25	80	mA
Holding current	I _H	V _D =12V;I _{GT} =0.1A		15	60	mA
On-State Voltage	V _T	I _T =40A		1.4	1.75	V
Gate Trigger Voltage	V _{GT}	V _D =12V;I _T =0.1A		0.6	1.5	V
		V _D =V _{DRM(max)} , I _T =0.1A, T _J =125℃	0.25	0.4		
Off-State Leakage Current	I _{DRM}	V _D =V _{DRM(max)} , V _R =V _{RRM(max)} ,		0.2	1.0	mA
	I _{RRM}	T _J =125℃		0.2	1.0	
DYNAMIC CHARACTERISTICS						
Critical Rate of Rise of off-state Voltage	dV _D /dt	V _{DM} =67%V _{DRM(max)} , T _J =125℃, Exponential Waveform Gate Open Circuit	200	300		V/μs
Gate Controlled Turn-on Time	t _{gt}	V _D =V _{DRM(max)} , I _G =0.1A dI _G /dt=5A/μs, I _{TM} =40A		2		μs
Circuit Commutated Turn-Off Time	t _Q	I _{TM} =50A, V _R =25V, R _{GK} =100Ω dI _{TM} /dt=30A/μs, dV _D /dt=50V/μs		70		μs

BT152

SCR

■ TYPICAL CHARACTERISTICS (1)




Fig.1. Maximum on-state dissipation, P_{tot} , versus average on-state current, $I_{T(AV)}$, where $a = \text{form factor} = I_{T(RMS)} / I_{T(AV)}$.




Fig.2. Maximum permissible non-repetitive peak on-state current I_{TSM} , versus pulse width t_p , for sinusoidal currents, $t_p \leq 10\text{ms}$.




Fig.3. Maximum permissible rms current $I_{T(RMS)}$, versus mounting base temperature T_{mb} .




Fig.4. Maximum permissible non-repetitive peak on-state current I_{TSM} , versus number of cycles, for sinusoidal currents, $f = 50\text{Hz}$.




Fig.5. Maximum permissible repetitive rms on-state current $I_{T(RMS)}$, versus surge duration, for sinusoidal currents, $f = 50\text{Hz}$; $T_{mb} \leq 103^\circ\text{C}$.




Fig.6. Normalised gate trigger voltage $V_{GT}(T_j) / V_{GT}(25^\circ\text{C})$, versus junction temperature T_j .

BT152

SCR

■ TYPICAL CHARACTERISTICS (2)




Fig. 7. Normalised gate trigger current $I_{GT}(T_J) / I_{GT}(25^\circ\text{C})$, versus junction temperature T_J .




Fig. 8. Normalised latching current $I_L(T_J) / I_L(25^\circ\text{C})$, versus junction temperature T_J .




Fig. 9. Normalised holding current $I_H(T_J) / I_H(25^\circ\text{C})$, versus junction temperature T_J .




Fig. 10. Typical and maximum on-state characteristic.




Fig. 11. Transient thermal impedance $Z_{th(j-mb)}$ versus pulse width t_p .





Fig. 12. Typical, critical rate of rise of off-state voltage, dV_D/dt versus junction temperature T_J .

BT152

SCR

TO-220F PACKAGE OUTLINE DIMENSIONS





Symbol	Dimensions In Millimeters	
	Min	Max
A	4.300	4.750
A1	0.7 REF	
A2	2.300	2.850
A3	2.500	2.900
b	0.380	0.420
b1	1.220	1.280
C	1.08	1.200
c	0.480	0.520
D	10.15	10.450
E	15.700	15.950
e	2.574 TYP	
F	3.470 REF	
y	3.200 REF	
h	0.000	0.800
L	28.780	28.900
L1	2.990	3.100

TO - 220F PACKING INFORMATION

Package version	Tube dimensions LxWxH (mm)	Per Tube (pcs)	Tube per box	Inner box dimensions LxWxH (mm)	PCS/ Inner box	Outer box dimensions LxWxH(mm)	PCS/ Outer box
TO-220F	530*32*7	50	20	580*155*50	1000	602*277*188	5000

■ TO - 252 Package Outline Dimensions



■ TO - 252 Packing Information

Package version	Reel dimensions $\phi \times H$ (mm)	Per Reel (pcs)	Reels per box	Inner box dimensions $L \times W \times H$ (mm)	Outer box (pcs)	Outer box dimensions $L \times W \times H$ (mm)
T0-252	$\phi 330 \times 20$	2500	2	360*340*50	25000	375*375*280