



1. 极数 Number of poles: 2-16
2. 工作温度 Working Temperature: -40°C-+85°C
3. 额定电压 Voltage rating :125V AC
4. 额定电流 Rated current :1A
4. 接触电阻 Contact resistance: ≤30mΩ
5. 绝缘电阻 Insulation resistance: ≥100MΩ
6. 耐压 Withstand voltage :250V AC
7. 端子 Terminal :铜合金 Copper Alloy
外壳 Housing :LCP



PCB.焊接图
PCB.WELDING DRAWING

Part No	PIN	A	B	C
XY-SM2L-MXS-TB	2	1.25	4.30	7.05
XY-SM3L-MXS-TB	3	2.50	5.55	8.30
XY-SM4L-MXS-TB	4	3.75	6.80	9.55
XY-SM5L-MXS-TB	5	5.00	8.05	10.80
XY-SM6L-MXS-TB	6	6.25	9.30	12.05
XY-SM7L-MXS-TB	7	7.50	10.55	13.30
XY-SM8L-MXS-TB	8	8.75	11.80	14.55
XY-SM9L-MXS-TB	9	10.00	13.05	15.80
XY-SM10L-MXS-TB	10	11.25	14.30	17.05
XY-SM11L-MXS-TB	11	12.50	15.55	18.30
XY-SM12L-MXS-TB	12	13.75	16.80	19.55
XY-SM13L-MXS-TB	13	15.00	18.05	21.80
XY-SM14L-MXS-TB	14	16.25	19.30	22.05
XY-SM15L-MXS-TB	15	17.50	20.55	23.30
XY-SM16L-MXS-TB	16	18.75	21.80	24.55

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
≥0~2<	±0.20	±0.5°	APR. Alex	TITLE: WAFER 1.25 立贴	
≥2~5<	±0.30		CHK. Jack	DWG NO. XY-SMNL-MXS-TB	
≥5	±0.50		DRA. Can	PROJ. CUSTOMER DRAWING	
SIZE	A4	SCALE	1:1	SHEET	1/1
		REV.		A	