


REV.	EC#	DESCRIPTION	DATE	DRAWN	CHECK	APPROVED
1.00		初版发行	2018-04-22			

技术参数 SPECIFICATIONS

1. 线数 (Poles) : 2~20
2. 适用线规 (Applicable wires) : AWG26#~22#
3. 适应基板厚度 (Applicable PC board thickness) : 1.6mm
4. 温度范围 (Temperature range) : -25 ~85
5. 额定电压 (Voltage rating) : 250V.Ac/Dc
6. 额定电流 (Current rating) : 3A
7. 接触电阻 (Contact resistance) : $\leq 0.01\Omega$
8. 绝缘电阻 (insulation resistance) : $\geq 1000M\Omega$
9. 耐压 (Withstand voltage) : 1000V.Ac/1min
10. 材料 (Material) : 孔座 (Housing) : 尼龙 (PA66) UL94V-0 针座 (Wafer) : PA-9T UL64V-0 端子 (Terminal) : 磷青铜 (Phos.bronze Tin/plated)



技术要求:

- 1) 材质: 见附表;
- 2) 电镀: 见附表;
- 3) 塑件表面平整、光洁、无毛刺、气泡、烧焦、变形、浇口无拉伤、多料或缺料等不良现象;
- 4) 端子表面无氧化、电镀不良等现象。

GENERAL TOLERANCES			
DIM	TOL	DIM	DEG
X		X°	±3.00°
X.X	±0.35	X.X°	±2.00°
X.XX	±0.25	X.XX°	±1.00°
X.XXX	±0.15	X.XXX°	

1	端子	1 PCS	材质：高精磷铜 抗拉, 电镀: 镀亮锡		
NO.	NAME	Q'TY	DESCRIPTION		
 韩下® 深圳市韩下电子有限公司					
DRAW :	黄彬	2018-04-22	TITLE:		DRAW NAME:
DESIGN:			压线端子		HX-2510-T
CHECK:	张伟	2018-04-22	SERIES: 2510 SERIES		DRAW NO.
APPROVED	罗小春	2018-04-22	P/N:		UNIT:
CUSTOMER DRAWING			REV. 1.00	SCALE N/A	SHEET: 1/1
					