


# CQ3225X7S106K500NRL

Automotive







Description : 1210(inch base) / 3225(mm base), X7S, 10 $\mu$ F,  $\pm$ 10%, 50V



Specifications		
Capacitance	10.00	$\mu$ F
Tolerance	$\pm$ 10%	
Temperature Characteristic	X7S	(-55 to 125°C)
Temperature Coefficient	$\pm$ 22%	
Rated Voltage	50	V

Shape & Dimensions		
Size code	(mm/inch)	3225 / 1210
L	(mm)	3.20 $\pm$ 0.40
W	(mm)	2.50 $\pm$ 0.25
T	(mm)	2.50 $\pm$ 0.25

## Electrical Characteristics Data



\* The data provided is for reference only, and electrical characteristics may vary based on measurement conditions or environment. This datasheet is subject to change without prior notice.