

	REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A			2024.11.12	
A2	N/A			2026.03.09	

PART NO.:

X9127 W V-12 S-9T SN RE

Series No

Category:W—Wafer

Welding Board Angle:R-Stright 90°

Row No.Pin No:XX-04~26Pin

Special No:S-No groove, has corners

Material: 9T-PA9T UL 94V-0;PT-PBT 94V-0

Plating Category: SN-Bright tin Plating

Color: RE—Red ; RD—Purplish red

■ SPECIFICATIONS

- Voltage rating:500V AC/DC
- Current rating:1A AC/DC
- Withstanding Voltage:1000V AC/minute
- Temperature range:-40°C~+125°C
- Insulation resistance:≥1000MΩ
- Contact resistance ≤20mΩ
- After environment testing ≤30mΩ

Poles	Dimensions(mm)	Poles	Dimensions(mm)
	A		A
4	2.54	16	17.78
6	5.08	18	20.32
8	7.62	20	22.86
10	10.16	22	25.40
12	12.70	24	27.94
14	15.24	26	30.48

X9127WV-12S-PTS NRE	Red	PBT UL 94V-0	Brass	Tin-Plated	X9127F
X9127WV-12S-9TSNRD	purplish red	PA9T UL 94V-0			
X9127WV-12S-9TSNRE	Red				
PART NO	Color	Material	Material(Pin)	Finish(Pin)	Suitable XKE Female

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERAUCES	

XKLB 星城
Connection

DESIGN

CHECKED

APPROVE

VIEW:

UNIT: mm/i

SIZE: A4

MODEL TYPE:	1.27mm Crimp Style Connectors
-------------	-------------------------------

PART NO.:

DWG NO.:

SCALE	PAGE	REVISION
N/A	1/1	A2

XKB INDUSTRIAL PRECISION CO.,LIMITED

www.helloxkb.com www.helloxkb.cn www.xk-dq.cn

PCB Layout

