

High Current IO+/- 0.4/0.6A HALF-BRIDGE DRIVER

General Description

The DR600SAX Fully operated to +600V is high voltage, high speed power MOSFET and IGBT driver with dependent high and low side referenced output channels.

The logic input is compatible with standard CMOS or LSTTL output, down to 3.3V logic. The output drivers feature a high pulse current buffer stage designed for minimum driver cross-conduction. The floating channel can be used to drive an N-channel power MOSFET or IGBT in the high side configuration which operates up to 600 volts.

Product Summary

V _{OFFSET}	600V max
I _{O+/-}	0.4A / 0.6A
V _{OUT}	4.8V ~ 20V
t _{on/off} (typ.)	750/170ns
Deadtime (typ.)	500ns
Work Tem	-40 ~150 °C

Key Features

- Floating channel designed for bootstrap operation
- Fully operational to +600V
- Tolerant to negative transient voltage dV/dt immune
- Gate drive supply range from 4.8 to 20V
- Undervoltage lockout
- 3.3V, 5V and 15V input logic compatible
- Cross-conduction prevention logic
- Matched propagation delay for both channels

Applications

- Home appliances
- Industrial applications and drives
- Motor drivers
- DC- AC Converter, PMDC and PMAC motors
- Induction heating
- HVAC

Packages




8-Lead SOP

Product information

Base Part Number	Package Type	Standard OUT		V _{OFFSET}	Logic Control
		IO+	IO-		
DR600 SAX	SOP8	0.4A	0.6A	600V	HIN & LIN

Pin Assignments





DR600
SAX

Pin Function

Number	Symbol	Description
1	VCC	Low side and logic fixed supply
2	HIN	Logic input for high side gate driver outputs (HO), in phase
3	LIN	Logic input for low side gate driver outputs (LO), in phase
4	COM	Low side return
5	LO	Low side gate drive output
6	VS	High side floating supply return
7	HO	High side gate drive output
8	VB	High side floating supply

Typical Connection



Much Big POWER application

Absolute Maximum Ratings

Absolute maximum ratings indicate sustained limits beyond which damage to the device may occur. All voltage parameters are absolute voltages referenced to COM. The thermal resistance and power dissipation ratings are measured under board mounted and still air conditions.

Symbol	Definition	Min.	Max.	Units
VB	High side floating absolute voltage	-0.3	600	V
VS	High side floating supply offset voltage	VB-25	VB+0.3	
VHO	High side floating output voltage	VS-0.3	VB+0.3	
VLO	Low side output voltage	-0.3	Vcc+0.3	
Vcc	Low side and logic fixed supply voltage	-0.3	25	
VIN	Logic input voltage (HIN & LIN)	-0.3	Vcc+0.3	
dVS/dt	Allowable offset supply voltage transient	—	55	V/ns
P _D	Package power dissipation @ TA ≤ +25°C	—	0.625	W
RthJA	Thermal resistance, junction to ambient	—	200	°C/W
TJ	Junction temperature	-35	150	°C
TS	Storage temperature	-55	175	
TL	Lead temperature (soldering, 10 seconds)	—	300	

Recommended Operating Conditions

The Input/Output logic timing diagram is shown in Figure 1. For proper operation the device should be used within the recommended conditions. The VS offset rating is tested with all supplies biased at 15V differential.

Symbol	Definition	Min.	Max.	Units
VB	High side floating supply absolute voltage	VS + 4.8	VS + 20	V
VS	High side floating supply offset voltage	-25	600	
VHO	High side floating output voltage	VS	VB	
VLO	Low side output voltage	0	VCC	
VCC	Low side and logic fixed supply voltage	4.8	20	
VIN	Logic input voltage (HIN&LIN)	0	VCC	
TA	Ambient temperature	-40	125	°C

Electrical Characteristic

$V_{CC} = V_{BS} = V_{BIAS} = 15V$, $C_L = 1000pF$, $T_A = 25^{\circ}C$, unless otherwise specified.

Symbol	Definition	Min.	Typ.	Max.	Units	Test Conditions
t_r	Turn-on rise time	—	70	—	ns	
t_f	Turn-off fall time	—	40	—		
t_{on}	Turn-on propagation delay	—	750	—		$V_S = 0V$
t_{off}	Turn-off propagation delay	—	170	—		$V_S = 400V$
DT	Deadtime, LS turn-off to HS turn-on & HS turn-on to LS turn-off	—	500	—		
MT	Delay matching, HS & LS turn-on/off	—	—	70		


Electrical Characteristic

$V_{CC} = V_{BS} = V_{BIAS} = 15V$, $T_A = 25^{\circ}C$, unless otherwise specified.

Symbol	Definition	Min.	Typ.	Max.	Units	Test Conditions
Low Side Power Supply Characteristics						
V _{CCUV+}	VCC supply undervoltage positive going threshold	4.0	4.7	5.2		
V _{CCUV-}	VCC supply undervoltage negative going threshold	3.8	4.5	5.0		
V _{CCHYS}	VCC supply under-voltage lockout hysteresis	0	0.2	—		
High Side Floating Power Supply Characteristics						
V _{BSUV+}	VBS supply undervoltage positive going threshold	4.0	4.7	5.2		
V _{BSUV-}	VBS supply undervoltage negative going threshold	3.8	4.5	5.0		
V _{BSUVHS}	High side VBS supply under-voltage lockout hysteresis ⁶	0	0.2	—		
IQCC	Quiescent VCC supply current	—	10	—	uA	V _{IN} =0V or 5V
IQBS	Quiescent VBS supply current	—	10	—		V _{IN} =0V or 5V
ILK	Offset supply leakage current	—	—	3		VB =VS =400V
VIH	Logic “1” (HO) & Logic “0” (LO) input voltage	3	—	—	V	VCC =5V to 20V
VIL	Logic “0” (HO) & Logic “1” (LO) input voltage	—	—	0.8		VCC =5V to 20V
IIN+	Logic “1” input bias current	—	3	10	uA	V _{IN} =5V L _{IN} = 0V
IIN-	Logic “0” input bias current	—	—	1		V _{IN} =5V L _{IN} = 0V
VOH	High level output voltage, V _{BIAS} - VO	—	—	100	mV	Io = 0A
VOL	Low level output voltage, VO	—	—	100		Io =0A


IO+	Output high short circuit pulsed current	—	400	—	mA	VO= 0V, V _{IN} = V _{IH} PW ≤ 10 us
IO-	Output low short circuit pulsed current	—	600	—		VO = 15V, V _{IN} = V _{IL} PW ≤ 10 us

Block Diagram







DR600
SAX

Time waveform




DR600
SAX

Time waveform




Switching Time Waveform Definitions

Delay matching time Definitions




Deadtime Waveform Definitions

Packaging information




Symbol	Dimensions In Millimeters	
	Min	Max
A	1.350	1.750
A1	0.100	0.250
A2	1.350	1.550
b	0.330	0.510
c	0.170	0.250
D	4.700	5.100
E	3.800	4.000
E1	5.800	6.200
e	1.270(BSC)	
L	0.400	1.270
θ	0°	8°

Tape & Reel 8-lead SOP



CARRIER TAPE DIMENSION FOR 8SOP

Code	Metric		Imperial	
	Min	Max	Min	Max
A	7.90	8.10	0.311	0.318
B	3.90	4.10	0.153	0.161
C	11.70	12.30	0.46	0.484
D	5.45	5.55	0.214	0.218
E	6.30	6.50	0.248	0.255
F	5.10	5.30	0.200	0.208
G	1.50	n/a	0.059	n/a
H	1.50	1.60	0.059	0.062



REEL DIMENSIONS FOR 8SOP

Code	Metric		Imperial	
	Min	Max	Min	Max
A	329.60	330.25	12.976	13.001
B	20.95	21.45	0.824	0.844
C	12.80	13.20	0.503	0.519
D	1.95	2.45	0.767	0.096
E	98.00	102.00	3.858	4.015
F	n/a	18.40	n/a	0.724
G	14.50	17.10	0.570	0.673
H	12.40	14.40	0.488	0.566