


SGBJ



■特征 Features

- 玻璃钝化芯片
Glass passivated chip
- 低反向漏电流
Low reverse leakage current
- 高耐浪涌电流能力
High surge current capability
- UL 档案编号# E249161
UL recognized file # E249161
- 符合 RoHS 指令 2011/65/EU
Compliant to RoHS directive 2011/65/EU

■应用范围 Applications

- 伺服器
Server
- 变频器
Frequency converter
- 工业电源
Industrial power supply

■机械参数 Mechanical Data

- 本体: SGBJ
Case : SGBJ
- 极性: 极性符号铸在管体上
Polarity: Polarity symbols being marked on body
- 安装扭矩: 8.0kgf.cm
Mounting torque: 8.0kgf.cm max
- 重量: 约 10 克
Weight : About 10 grams

关键参数 KEY PARAMETERS

参数 PARAMETER	数值 VALUE	单位 UNIT
$I_{F(AV)}$	60	A
V_{RRM}	800-1600	V
I_{FSM}	500	A
Package	SGBJ	

■最大额定值 Maximum Ratings @ $T_a = 25^\circ\text{C}$ unless otherwise noted

参数 PARAMETER	符号 SYMBOL	SGBJ6008	SGBJ6010	SGBJ6012	SGBJ6016	单位 UNIT
反向重复峰值电压 Maximum recurrent peak reverse voltage	V_{RRM}	800	1000	1200	1600	V
平均整流输出电流 Average rectified output current	$I_{(AV)}$	60				A
最大正向浪涌电流, 8.3ms 单半正弦波叠加在额定负载上 Peak surge forward current, 8.3ms single half sine-wave superimposed on rated load	I_{FSM}	500				A
热容值, 1ms< t < 8.3ms, $T_j = 25^\circ\text{C}$, 单个二极管 Rating for fusing, 1ms< t < 8.3ms, $T_j = 25^\circ\text{C}$, Rating of per diode	I^2t	1037.5				A^2s
结温 Junction temperature	T_j	$-55 \sim +150$				$^\circ\text{C}$
存储温度 Storage temperature	T_{STG}	$-55 \sim +150$				$^\circ\text{C}$
绝缘耐压, 端子与外壳之间外加交流电 1 分钟 Dielectric strength, terminals to case AC 1 minute	V_{dis}	2.5				KV

■电性特性 **Electrical Characteristics** @ Ta = 25℃ unless otherwise noted

参数 PARAMETER	条件 CONDITIONS	符号 SYMBOL	额定值 RATED VALUE	单位 UNIT
正向峰值电压 Peak Forward Voltage	$I_F = 30\text{ A}$	V_F	1.1	V
反向峰值电流 Peak Reverse Current	VR=VRRM, 脉冲测试, 单个二极管的额定值 VR=VRRM, Pulse measurement Rating of per diode	I_R	5	μA
			500	

■热特性 **Thermal Characteristics** @ Ta = 25℃ unless otherwise noted

参数 PARAMETER	符号 SYMBOL	额定值 RATED VALUE	单位 UNIT
结到环境的热阻, 无散热片 Junction to ambient thermal resistance, without heatsink	$R_{\theta JA}$	18	°C/W
结到管壳的热阻, 有散热片 Junction to case thermal resistance, with heatsink	$R_{\theta JC}$	1.2	°C/W

■特性曲线 **Characteristic Curve**

FIG1.Derating Curve For Output Rectified Current

图 1. 电流降额曲线




FIG2.Maximum Non-Repetitive Peak Forward Surge Current Per Bridge Element

图 2. 最大正向不重复峰值浪涌电流




FIG3.Typical Reverse Characteristics Per Bridge Element

图 3. 典型反向特性





FIG4.Typical Forward Characteristics Per Bridge Element

图 4. 典型正向特性



Package Outline Information Dimensions in inches (mm)

CASE: SGBJ

