







REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



Part No	Pin	A	B	C
JXT-AFC10-AS4P-H25	4	3.00	5.03	11.10
JXT-AFC10-AS5P-H25	5	4.00	6.03	12.10
JXT-AFC10-AS6P-H25	6	5.00	7.03	13.10
JXT-AFC10-AS7P-H25	7	6.00	8.03	14.10
JXT-AFC10-AS8P-H25	8	7.00	9.03	15.10
JXT-AFC10-AS9P-H25	9	8.00	10.03	16.10
JXT-AFC10-AS10P-H25	10	9.00	11.03	17.10
JXT-AFC10-AS11P-H25	11	10.00	12.03	18.10
JXT-AFC10-AS12P-H25	12	11.00	13.03	19.10
.....		...		
JXT-AFC10-AS40P-H25	40	(40-1)*1.0	(40+1)*1.0+0.03	(40+6)*1.0+0.10



适用扁平线(Applicable Flat Cable)



适用线路板(PCB LAYOUT)

序号	品名	材质
1	1.0胶芯(H2.5)	LCP UL94V-0 本色
2	1.0上接端子(H2.5)	铜合金/表面镀锡
3	1.0卧式后盖(H2.5)	LCP UL94V-0 黑色
4	1.0卧式焊片(H2.5)	铜合金/表面镀锡

技术指标:

1. 塑件表面应光洁, 无毛边、无明显收缩、缺陷、裂纹等现象.
2. 温度范围: $-25^{\circ}\text{C} \sim +85^{\circ}\text{C}$.
3. 额定电压: 50V, AC/DC.
4. 接触电阻: $\leq 0.03\Omega$.
5. 绝缘电阻: $\geq 500M\Omega$

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
.X±0.30	.X°±5°	PART NO.	TITLE: 1.0 Pitch H2.5 ZIF		
.XX±0.20	.XX°±2°	JXT-AFC10-ASNP-H25	R/A Type Top CONN.		
.XXX±0.05	.XXX°±1°	DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia			
MATERILA	---	APPD: Ava			
FINISH	---			SCALE N:A	SHEET 1/1