


NO.	ECN NO.	DESCRIPTION	DATE
-----	---------	-------------	------

客户图



Note:

- 1: Material(材料) :
Barrel: Brass C3604 (针管: 黄铜 C3604)
Plunger: Brass C3604 (针头: 黄铜 C3604)
Spring: SUS304 (弹簧: SUS304)
- 2: Plating(电镀) :
Barrel: 3u' Au over 50~80u' Ni(针管: 镀金3u', 镍底50~80u'.)
Plunger: 3u' Au over 50~80u' Ni (针头: 镀金3u', 镍底50~80u'.)
Spring: No plated (弹簧: 不电镀)
- 3: Electrical(电气特性) :
Rated Current & Voltage: DC 12V;1A (额定电压&电流: 直流12V,1A)
Contact Resistance: 50 mohm Max. at working height.
接触电阻: 最大50毫欧 (在工作高度状态下)
- 4: Mechanical(机械性能) :
Force: 120g±20% at working height. (120g±20% 在工作高度)。
Durability: 10,000 cycles(min) (寿命: 10000次)
- 5: WorkTemperature(工作环境):
Withstanding Higt Temperature: 280t
Operational Temperature: - 20t~ + 70t

深圳市鑫探技术有限公司										HTTP://WWW.XYZPOGOPIN.COM										TEL:0755-28773277 FAX:0755-28891353													
										SCALE:			N/A			UNIT			mm			THE UNMARKED TOLERANCE ARE AS BELOW : LENGTH X.XX ±0.05mm X.X ±0.10mm X. ±0.20mm ANGLE X.XX ±0.50° X.X ±1.00° X. ±2.00°											
SHEET:			1 of 1			PROJECTION						D.0																					
DATE:			2026.4.21			VER.																											
															DESIGNED BY:			DWG. NO.			YZ182115060F-02												
															CHECKED BY:						TITLE:			Pogo pin 连接器									
															APPROVED BY:																		