











NOTES:

1.MATERIAL:

- 1.1 Housing:High Temperature Thermoplastic UL94V-0; Color Black.
- 1.2 Terminal:Copper Alloy,T=0.12mm.
- 1.3 Shell:Stainless Steel,T=0.20mm.


2.FINISH:

- 2.1 Terminal:Plated Gold on The Contact Area and Solder Tails
- 2.2 Peg:Plated Gold on the Solder Tails,

3.SPECIALITY:

- 3.1 Rated current:0.5A
- 3.2 Rated voltage:50V
- 3.3 Contact Resistance:80mΩMAX
- 3.4 Insulation Resistance:100MΩMIN 100V DC
- 3.5 Dielectric withstanding voltage: 100V AC.
- 3.6 Solder ability:245±5°C,5±0.5s.
- 3.7 Operating condition:Temperature: -40°C~+85°C Humidity: 80% R.H MAX

NANO SIM CARD	
Pin No.	NAME
C1	VCC OF SIM
C2	RST OF SIM
C3	CLK OF SIM
C5	GND OF SIM
C6	VPP OF SIM
C7	I/O OF SIM
C4/C8	N/A
S/W	Switch Pin





PAD AREA

RECOMMENDED PCB LAYOUT

GENERAL TOLERANCE ±0.05


Circuit Diagram for Card Detect Switch



③	TERMINAL	6	C5210-EH,T=0.12	G/F PLATING	
②	BASE INSULATOR	1	LCP+GF30%	BLACK	
①	SHELL	1	SUS304-H,T=0.15	AU/Ni PLATING	
NO.	PART NAME	Q'TY	DESCRIPTION	NOTE	
TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.±0.50	X.*±2°	PART NO. JXT-NANO-305-7P		TITLE: 7pin 1.4h higne namo sim card conn.	
X.X±0.20	X.X*±1°				
X.XX±0.10					
UNITS	mm	DESIGN: Ethan		MANUFACTURE DWG	
MATERILA	— — —	CHED: Olvia			
FINISH	— — —	APPD: Ava			
				SCALE N:A	SHEET 1/2

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN




图示(一) 载带



NOTES:

- 1,每盘包装1500PCS产品.
包装要求如图示(二)
- 2,每箱包装数量16500PCS.纸箱外则以胶带封口成(工)字型.
- 3,上载带剥离不速度:300mm/minutes.
- 4,卷带封合力小于100G.

图示(二)圆盘包装



TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.±0.50	X.*±2°	PART NO. JXT-NANO-305-7P	TITLE: 7pin 1.4h higne namo sim card conn.	
X.X±0.20	X.X°±1°			
X.XX±0.10				
UNITS	mm	DESIGN: Ethan	MANUFACTURE DWG	
MATERILA	---	CHED: Olvia		
FINISH	---	APPD: Ava		SCALE N:A
				SHEET 2/2