

MESSRS.**SPECIFICATION FOR APPROVAL****承 認 书**

Product	DYNAMIC SPEAKER
Part No.	HDK-280844-003 (HF)
Customer	
Customer Part No.	

Approved By	Checked By	Made By
王台平 MAR-20-2023	曹丽萍 MAR-20-2023	LILY MAR-20-2023

常 州 华 龙 电 子 有 限 公 司**DRAGONSTATE ELECTRONIC CORPORATION**

中国江苏省常州市新区电子园新四路 36 号

Tel: +86-519-85110078. 86-519-85106698, Fax: +86-519-85101081

1.Specification

HDK-280844-003 (HF)

ITEM		SPECIFICATIONS	
01	Type	Dynamic speaker	
02	Dimension	External diamete28 mm	
03	Rated Input Power	0.5W	
04	Max. Input Power	1.0W for 1 minute	
05	Impedance	8 ohm $\pm$ 15% at 1000 Hz	
06	Resonance Frequency (Fo)	750Hz $\pm$ 20% at Fo, 0.5W	
07	Sensitivity (S.P.L.)	97dB (0.5W / 0.1m) $\pm$ 3 dB	atAVE 0.6K,0.8K,1.0K,1.2 KHz.
08	Frequency Range	Fo – 20K Hz	
09	Total Harmonics Distortion	Max. 10% at 1K Hz ,0.5W.	
10	Weight	5.0g $\pm$ 0.3g	
11	Appearance	Should not exist any obstacle to be harmful to normal operation; damages, cracks, rusts and distortions, etc.	
12	Operation Test	Must be normal at program source 0.5W	
13	Buzz, Rattle, etc.	Should not be audible at 2.0V sine Wave between 300 to 5KHz	
14	Polarity	When positive voltage is applied to the terminal marked (+), diaphragm should move to the front.	
15	Terminal Strength	Capable of withstand 1kg load for 30 seconds without resulting in any damage or rejection.	
16	Temperature	Operating temperature: -30°C to +70°C Storage temperature: -40°C to +80°C	

1. MEASURING METHOD

2-1 .Test Condition

STANDARD

Temperature : 15 ~ 35°C

Relative humidity : 25% ~ 85%,

Atmospheric pressure : 860mbar to 1060mbar.

JUDGEMENT

Temperature : 20±3°C

Relative humidity : 60% ~ 70%,

Atmospheric pressure : 860mbar to 1060mbar

2-2 . Standard Test Fixture


1.Input Power : 0.5W(2.0V)

2.Zero Level : -dB


3.Mode : SPEAKER

4.potentiometer Range : 50dB


5.Sweep Time : 0.5sec




2-3. Frequency Response Curve



3.Dimension



4. Reliability Test

Items.		Specifications
01	High temp. Test	Keep 96 hours at $+75^{\circ}\text{C} \pm 3^{\circ}\text{C}$ and leave 3 hours in normal temperature and then check
02	Low temp. Test	Keep 96 hours at $-40^{\circ}\text{C} \pm 3^{\circ}\text{C}$ and leave 3 hours in normal temperature and then check
03	Humidity test	Keep 96 hours at $+40^{\circ}\text{C} \pm 3^{\circ}\text{C}$ relative humidity 90% and leave 3 hours in normal temperature and then checked.
04	Temp./Humidity cycle	The part shall be subjected 5 cycles. One cycle shall be 12 hours and consist of; 
05	Thermal cycle test.	Low temperature: $-30^{\circ}\text{C} \pm 3^{\circ}\text{C}$, temperature: $+75^{\circ}\text{C} \pm 3^{\circ}\text{C}$, cycle: 1 hour/cycle each, and then keep 5 cycles in a room.
06	Vibration	10~200~10Hz sin-wave sweep 15min. 5G(constant) X,Y, Z 3 direction. 2 hours each, total 6 hours.
07	Fix drop test	Fix on jig. Then drop from 152cm height to the concrete floor X,y, z 6 direction. 5 times each, total 30 times.
08	Free drop test	Free drop from 100cm height to the concrete floor X,y, z 6 direction. 1 times each, total 6 times.
09	Load test	Rated Power Pink noise is applied for 96 hours
10	Max Power test	Max power 1 min on - 2 min off 10 cycles.
11	Terminal strength test	Capable of withstand 1kg load for 30 seconds without resulting in any damage or rejection.

SOLDERING CONDITION

Recommend using constant branding iron in **30W**, and in temperature range **$350 \pm 10^{\circ}\text{C}$** .

Soldering time **2** seconds.