



深圳市佑驰电子有限公司

Specification for Approval

产品名称: T-core小颗
规格型号: HPLB-201212-R11-M
产品编号: _____
日期: 2026-1-20

- 1、本承诺书的内容更改需经过双方确认，任一方单独的修改均视为无效。
- 2、本承诺书在送达客户后，请给予承认并即签回，如无签回下订单的，我司有权以此承诺书标准生产，并表示购买方默认许可。

核准	审核	制作
	Aaron	Ada

High Current, Power Inductors



Description

- Halogen Free
- 125°C maximum total temperature operation
- Powder iron core material
- Magnetically shielded, low EMI
- High current carrying capacity, Low core losses
- Frequency range up to 5 MHz
- RoHS compliant

Features

- 1.1 Metal material for large current and low loss.
- 1.2 High performance (Isat) realized by metal dust core.
- 1.3 Low loss realized with low Rdc.
- 1.4 Closed magnetic circuit design reduces leakage flux.
- 1.5 Vinyl thermal spray, better surface compactness.
- 1.6 Environmental requirements must comply with the QESP-44 document
- 1.7 100% lead (Pb) free meet RoHS2.0 and Halogen, Reach and other legal and regulatory requirements standard.

Applications

- Voltage Regulator Module (VRM)
- Multi-phase regulators
- Point-of-load modules
- Smart phone POL modules
- SSD modules
- Notebook regulators
- Battery power systems
- Graphics cards
- Data networking and storage systems



Environmental Data

- Storage temperature range: -55°C to +125 °C
- Operating temperature range: -5.5°C to +125°C (ambient plus self-temperature rise)
- Solder reflow temperature: J-STD-020 D compliant

Packaging

- Supplied in tape and reel packaging.

1. SHAPE AND DIMENSIONS



单位: mm

产品系列	L	W	T	a	A	B	C
HPLB-201212	2.0±0.2	1.2±0.2	1.20Max	0.70±0.2	2.10	0.50	1.30

2. Specifications

HPLB-201212(2.0*1.2*1.2mm)


产品类别 单位	感值 μH	直流电阻 DCR(mΩ)		温升电流 I _{rm} -(A)		饱和电流 I _a -(A)	
		-Typ.	Max.	-Typ.	Min.	-Typ.	Min.
HPLB-201212-R11-M	0.11	5.5	6.2	12.0	11.0	12.0	11.0

Notes

- All test data is referenced to 25 °C ambient
- Operating temperature range - 55 °C to + 125 °C
- I_{dc}(A) : DC current (A) that will cause an approximate ΔT of 40 °C (reference ambient temperature is 25 °C)
- I_{sat}(A) : DC current (A) that will cause L0 to drop approximately 30% . 5. 125 °C under worst case 50V DC shall be applied for 60s between the terminal and the Core
- The part temperature (ambient + temp rise) should not exceed operating conditions . Circuit design , component placement , PWB trace size and thickness , airflow and other cooling provisions all affect the part temperature . Part temperature should be verified in the end application .

3. Soldering Condition


(This is for recommendation, please customer perform adjustment according to actual application) Recommend Reflow Soldering Profile : (solder : Sn96.5 / Ag3 / Cu0.5)



Profile Feature	Lead (Pb)-Free solder
Preheat:	
Temperature Min (T_{smin})	150°C
Temperature Max (T_{smax})	200°C
Time (T_{smin} to T_{smax}) (t_s)	60 -120 seconds
Average ramp-up rate: (T_{smax} to T_p)	3°C / second max.
Time maintained above : Temperature (T_L)Time (t_L)	217°C 60-150 seconds
Peak Temperature (T_p)	260°C
Time within $+0^\circ\text{C}$ of actual peak Temperature (t_p) -5	10 seconds
Ramp-down Rate	6°C/second max.
Time 25°C to Peak Temperature	8minutes max.

4. Packing

The following dimensions are related to the actual fit of the machine , for reference only.



Series	W	A0	B0	D0	D1	E	F	K0	P0	P2	P1	T	Packing quantity
Tolerance	±0.10	±0.10	±0.10	+0.1/-0	±0.20	±0.10	±0.10	±0.10	±0.10	±0.10	±0.10	±0.05	
201212	8.0	1.5	2.35	1.5	1.0	1.75	3.5	1.35	4.0	2.0	4.0	0.22	3K

Dimension of Reel : (Unit: mm)

Type	A	B	C
All	±2.0	±2.0	±2.0
	178	60	13

