






ROHS



PCB LAYOUT

NOTE:

- 1.Current Rating 1.5A/contact terminal
- 2.Voltage Rating 30V DC
- 3.Insulation Resistance: 1000MEGA ohms MIN
- 4.Contact Resistance 30 milliohms MAX
- 5.Dielectric Withstanding Voltage: 500 V AC
- 6.Connector Mate and Unmate Force
Mate force:3.5 kgf(MAX) Unmate force:1kgf(MIN)

COSTOMER DRAWING			 深圳市莱联电子有限公司			
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
CHECK						
APPROVAL						
TOLERANCES ARE			TITLE	TYPE-A连接器4PIN弯插L18.8（直口）	REV.	A
30-150	±0.35	ANGLE	PART NO.	LAIL-TYPE-A-4P-02-WC	UNITS	mm
10-30	±0.2		DWG.NO.			
5-10	±0.15					
0-5	±0.1					
			Projection 			