


技术要求:

1. 塑件材料: PA66 (UL-94V-0)
2. 接触件: 黄铜镀锡
3. 接触电阻: $\leq 10m\Omega$
4. 绝缘电阻: $\geq 100M\Omega$
5. 额定电压: 250V AC DC
6. 额定电流: 2.0A AC DC
7. 耐压: 能承受 1000V AC/Minute
8. 工作温度: $-25^{\circ}\sim+85^{\circ}$
9. 可焊性试验: 浸锡面积 $\geq 95\%$ 温度 $235\pm 5^{\circ}$, 时间 2.5 ± 0.5 秒
10. 铅和镉等六大有害物质含量要符合环保要求.

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

Part No	Pin	A	B
JXT-PH2.0-2PWZ-P11	2	2.00	6.00
JXT-PH2.0-3PWZ-P11	3	4.00	8.00
JXT-PH2.0-4PWZ-P11	4	6.00	10.00
JXT-PH2.0-5PWZ-P11	5	8.00	12.00
JXT-PH2.0-6PWZ-P11	6	10.00	14.00
JXT-PH2.0-7PWZ-P11	7	12.00	16.00
JXT-PH2.0-8PWZ-P11	8	14.00	18.00
JXT-PH2.0-9PWZ-P11	9	16.00	20.00
JXT-PH2.0-10PWZ-P11	10	18.00	22.00
JXT-PH2.0-11PWZ-P11	11	20.00	24.00
JXT-PH2.0-12PWZ-P11	12	22.00	26.00
JXT-PH2.0-13PWZ-P11	13	24.00	28.00
JXT-PH2.0-14PWZ-P11	14	26.00	30.00
JXT-PH2.0-15PWZ-P11	15	28.00	32.00
JXT-PH2.0-16PWZ-P11	16	30.00	34.00
JXT-PH2.0-17PWZ-P11	17	32.00	36.00
JXT-PH2.0-18PWZ-P11	18	34.00	38.00
JXT-PH2.0-19PWZ-P11	19	36.00	40.00
JXT-PH2.0-20PWZ-P11	20	38.00	42.00

2	端子 Contact	黄铜	N*1	电镀(锡): 整个表面镀底镍 30u"MIN, 再镀锡 80u"MIN
1	基座 Wafer	PA66 (UL94V-0)	1	白色
序号	名称	材料	数量	备注

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X ±0.20	X.* ±10°	PART NO.	TITLE: PH2.0MM 弯针		
.XX ±0.10	.X* ± 8°	JXT-PH2.0-NPWZ-P11			
.XXX ±0.05	.XX* ± 5°	DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia			
MATERILA	— — —	APPD: Ava		SCALE	SHEET
FINISH	— — —			N:A	1/1