






SUGGESTED PCB LAYOUT
(COMPONENT SIDE)



- 技术要求:
1. 塑件材料: PA66 (UL-94V-0)
 2. 接触件: 黄铜镀锡
 3. 接触电阻: $\leq 20\text{m}\Omega$
 4. 绝缘电阻: $\geq 1000\text{M}\Omega$
 5. 额定电压: 250V AC DC
 6. 额定电流: 3.0A AC DC
 7. 耐压: 能承受 1000V AC/Minute
 8. 工作温度: $-25^{\circ}\sim+85^{\circ}$
 9. 可焊性试验: 浸锡面积 $\geq 95\%$ 温度 $235\pm 5^{\circ}$, 时间 2.5 ± 0.5 秒
 10. 铅和镉等六大有害物质含量要符合环保要求.

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

Part No	Pin	A	B
JXT-VH3.96-2PWZ-P11	2	3.96	7.92
JXT-VH3.96-3PWZ-P11	3	7.92	11.88
JXT-VH3.96-4PWZ-P11	4	11.88	15.84
JXT-VH3.96-5PWZ-P11	5	15.84	19.80
JXT-VH3.96-6PWZ-P11	6	19.80	23.76
JXT-VH3.96-7PWZ-P11	7	23.76	27.72
JXT-VH3.96-8PWZ-P11	8	27.72	31.68
JXT-VH3.96-9PWZ-P11	9	31.68	35.64
JXT-VH3.96-10PWZ-P11	10	35.64	39.60
...	...	...	...
JXT-VH3.96-20PWZ-P11	20	$(20-1)\times 3.96$	$(20+1)\times 3.96$

2	端子 Contact	黄铜	N*1	电镀(锡):整个表面镀底镍 30u"MIN,再镀锡80u"MIN		
1	基座 Wafer	LCP (UL94V-0)	1	米色		
序号	名称	材料	数量	备注		
TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd				
X.X	±0.20	X.*	±10°	PART NO.	TITLE: VH3.96MM 弯针 带扣	
.XX	±0.10	.X*	± 8°	JXT-VH3.96-NPWZ-P11		
.XXX	±0.05	.XX*	± 5°	DESIGN: Ethan	MANUFACTURE DWG	
UNITS	mm	CHED: Olvia				
MATERILA	— — —	APPD: Ava				
FINISH	— — —				SCALE N:A	SHEET 1/1