





REVISION			
LTR	DESCRIPTION	DATE	APP
A0	NEW RELEASE	05/20/2020	PECK




邀您使用(微信)小程序
碩方电子开关&连接器选型手册
手机扫码即可进入...

SCHEMATIC



P.C.B LAYOUT



- Note:
- 1. Material:
 - 1.1 Housing: High temperature thermoplastic, UL94v-0
 - 1.2 Orbit: High temperature thermoplastic, UL94v-0
 - 1.3 Contact: copper alloy;
Gold plated contact area; Tin plated solder area
 - 1.4 Shell: Stainless; Ni plated allover;
Gold plated solder area
 - 2. Specification:
 - 2.1 Current rating: **0.5A** Max
 - 2.2 Voltage rating: **24V** DC
 - 2.3 Dielectric withstanding voltage:
500V(AC) for 1 min.
 - 2.4 Contact resistance: 100mΩ Max.
 - 2.5 Insulation resistance: 1000MΩ min.
 - 2.6 Temperature range: -25°C~85°C
 - 2.7 Mating cycle: 5000 cycles min
 - 2.8 Insert force: 40N Max
Extraction force: 0.5~40N



DIMENSION CLASSIFICATION		台灣碩方精密電子科技有限公司 TAIWAN SOFENG PRECISION ELECTRONIC CO., LTD		開關, 連接器 SOFENG	
■ : CRITICAL ☒ : MAJOR		TITLE		PJ-308 耳机插座 φ3.5mm 卧插式弯脚	
TOLERANCE TABLE		PART NO.		SERIES SD106	
.X	± 0.40	DWG NO.		SOF-G006	
.XX	± 0.25	APPROVED	Peck	SCALE	1:1
.XXX	± 0.10	CHECKED	Paul	UNIT	mm
ANGLE	± 2°	DRAWIN	David	REV	AO
		SHEET NO.		1/1	