



**MSB**



## Features

- The plastic package carries Underwriters Laboratory Flammability Classification 94V-0
- Idea for printed circuit board
- Glass passivated Junction chip
- Low reverse leakage
- High forward surge current capability
- High temperature soldering guaranteed 250°C/10 seconds at terminals

## Mechanical Data


**Case :** Molded plastic body

**Terminals :** Solder plated, solderable per MIL-STD-750, Method 2026

**Polarity :** Polarity symbol marking on body

**Mounting Position :** Any

**Weight :** 0.0034 ounce, 0.098 grams



Dimensions in inches and (millimeters)

## Maximum Ratings And Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified. Single phase half-wave 60Hz, resistive or inductive load, for capacitive load current derate by 20%.

| Parameter                                                                                             | SYMBOLS                          | FMB<br>40A  | FMB<br>40B | FMB<br>40D | FMB<br>40G | FMB<br>40J | FMB<br>40K | FMB<br>40M | UNITS                       |
|-------------------------------------------------------------------------------------------------------|----------------------------------|-------------|------------|------------|------------|------------|------------|------------|-----------------------------|
| Maximum repetitive peak reverse voltage                                                               | V <sub>RRM</sub>                 | 50          | 100        | 200        | 400        | 600        | 800        | 1000       | V                           |
| Maximum RMS voltage                                                                                   | V <sub>RMS</sub>                 | 35          | 70         | 140        | 280        | 420        | 560        | 700        | V                           |
| Maximum DC blocking voltage                                                                           | V <sub>DC</sub>                  | 50          | 100        | 200        | 400        | 600        | 800        | 1000       | V                           |
| Maximum average forward rectified current<br>at T <sub>L</sub> =100°C On glass-epoxy P.C.B (Note 1)   | I <sub>(AV)</sub>                | 4.0         |            |            |            |            |            |            | A                           |
| Peak forward surge current, 8.3ms single half<br>sine-wave superimposed on rated load                 | I <sub>FSM</sub>                 | 150.0       |            |            |            |            |            |            | A                           |
| Rating for fusing (t=8.3ms, T <sub>a</sub> =25°C)                                                     | I <sup>2</sup> <sub>t</sub>      | 93.37       |            |            |            |            |            |            | A <sup>2</sup> <sub>s</sub> |
| Maximum instantaneous forward voltage at 4.0A                                                         | V <sub>F</sub>                   | 1.30        |            |            |            |            |            |            | V                           |
| Maximum DC reverse current T <sub>A</sub> =25°C<br>at rated DC blocking voltage T <sub>A</sub> =125°C | I <sub>R</sub>                   | 5.0<br>200  |            |            |            |            |            |            | μA                          |
| Maximum reverse recovery time (Note 2)                                                                | T <sub>rr</sub>                  | 150         |            |            |            | 250        | 500        |            | ns                          |
| Typical junction capacitance (Note 3)                                                                 | C <sub>J</sub>                   | 23.0        |            |            |            |            |            |            | pF                          |
| Typical thermal resistance                                                                            | R <sub>qJA</sub>                 | 55.0        |            |            |            |            |            |            | °C/W                        |
| Operating junction and storage temperature range                                                      | T <sub>J</sub> ,T <sub>STG</sub> | -55 to +150 |            |            |            |            |            |            | °C                          |

**Note:**1. Mounted on glass epoxy PC board with 1.3\*1.3mm solder pad

2. Reverse Recovery Test Conditions:  $I_F=0.5\text{A}$ ,  $I_R=1.0\text{A}$ ,  $I_{rr}=0.25\text{A}$

3. Measured at 1MHz and applied reverse voltage of 4.0V D.C.



## Ratings And Characteristic Curves

FIG. 1- DERATING CURVE OUTPUT RECTIFIED CURRENT




FIG. 2-MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT PER LEG




FIG. 3-TYPICAL FORWARD VOLTAGE CHARACTERISTICS






FIG. 4-TYPICAL REVERSE LEAKAGE CHARACTERISTICS




## Suggested Pad Layout



| Symbol | Unit (mm) | Unit (inch) |
|--------|-----------|-------------|
| A      | 1.8       | 0.071       |
| B      | 2.0       | 0.078       |
| C      | 5.50      | 0.216       |
| D      | 9.15      | 0.360       |
| E      | 2.6       | 0.102       |
| F      | 7.35      | 0.289       |




## Single Phase 3.0Amp Fast Recovery Bridge Rectifiers



| Symbol | Explanation                   |
|--------|-------------------------------|
| A      | Polarity Symbol               |
| B      | Product Name,X : 01.02.....10 |
|        |                               |

### Suggested Soldering Temperature Profile




#### Note

- Recommended reflow methods: IR, vapor phase oven, hot air oven, wave solder.
- The device can be exposed to a maximum temperature of 265°C for 10 seconds.
- Devices can be cleaned using standard industry methods and solvents.
- If reflow temperatures exceed the recommended profile, devices may not meet the performance requirements.

### Package Information

#### Carrier Dimension(mm)



| A0   | B0   | K0   | D0   | E    | F         |
|------|------|------|------|------|-----------|
| 6.90 | 8.60 | 1.65 | 1.55 | 1.75 | 7.50      |
| P0   | P1   | P2   | T    | W    | Tolerance |
| 4.0  | 12.0 | 2.0  | 0.30 | 16   | 0.1       |

#### Package Specifications

| Package | Reel Size | Reel DIA. (mm) | Q'TY/Reel (Kpcs) | Box Size (mm) | QTY/Box (Kpcs) | Carton Size (mm) | Q'TY/Carton (Kpcs) |
|---------|-----------|----------------|------------------|---------------|----------------|------------------|--------------------|
| MSB     | 13'       | 330            | 3                | 338           | 6              | 445*360*360      | 54                 |