

Product Summary

$V_{(BR)DSS}$	$R_{DS(on)TYP}$	I_D
150V	4.8mΩ@10V	220A


合肥矽普半导体

Siliup Semiconductor Technology Co., Ltd

技术 品质 服务
www.siliup.com


Feature

- Fast Switching
- Low Gate Charge and Rdson
- 100% Single Pulse avalanche energy Test


Applications

- Power switching application
- DC-DC Converter
- Power Management

Package



TOLL

Marking



015N05GH : Device Code
* : Month Code

Circuit diagram



Order Information

Device	Package	Unit/Tape
SP015N05GHTO	TOLL	2000

Absolute maximum ratings (Ta=25°C, unless otherwise noted)

Parameter	Symbol	Rating	Units
Drain-Source Voltage	V_{DS}	150	V
Gate-Source Voltage	V_{GS}	± 20	V
Continuous Drain Current (Tc=25°C)	I_D	220	A
Continuous Drain Current (Tc=100°C)	I_D	147	A
Pulsed Drain Current	I_{DM}	880	A
Single Pulse Avalanche Energy ¹	E_{AS}	1225	mJ
Power Dissipation (Tc=25°C)	P_D	298	W
Power Dissipation (Tc=100°C)	P_D	119	W
Thermal Resistance Junction-to-Case	$R_{\theta JC}$	0.42	°C/W
Storage Temperature Range	T_{STG}	-55 to 150	°C
Operating Junction Temperature Range	T_J	-55 to 150	°C

Electrical characteristics (Ta=25°C, unless otherwise noted)


Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Static Characteristics						
Drain-Source Breakdown Voltage	BV _{DSS}	ID=250μA , VGS=0V	150	-	-	V
Drain-Source Leakage Current	IDSS	VDS=120V , VGS=0V	-	-	1	uA
Gate-Source Leakage Current	IGSS	VGS=±20V , VDS=0V	-	-	±100	nA
Gate Threshold Voltage	VGS(th)	VDS=VGS , ID=250μA	2.8	3.2	3.8	V
Static Drain-Source On-Resistance	RDS(ON)	VGS=10V , ID=20A	-	4.8	6.0	mΩ
Gate Resistance	RG	VDS=75V , VGS=0V , f=1MHz	-	4.4	-	Ω
Dynamic characteristics						
Input Capacitance	Ciss	VDS=75V , VGS=0V , f=1MHz	-	5450	-	pF
Output Capacitance	Coss		-	545	-	
Reverse Transfer Capacitance	Crss		-	16	-	
Total Gate Charge	Qg	VDS=75V , VGS=10V , ID=20A	-	72	-	nC
Gate-Source Charge	Qgs		-	24	-	
Gate-Drain Charge	Qgd		-	16	-	
Gate Plateau Voltage	Vplateau		-	4.7	-	
Switching Characteristics						
Turn-On Delay Time	Td(on)	VDD=75V , VGS=10V , RG=3.0Ω , ID=20A	-	14.6	-	nS
Rise Time	Tr		-	22	-	
Turn-Off Delay Time	Td(off)		-	30	-	
Fall Time	Tf		-	11.6	-	
Diode Characteristics						
Diode Forward Voltage	VSD	VGS=0V , IS=1A , TJ=25℃	-	-	1.2	V
Maximum Body-Diode Continuous Current	IS		-	-	220	A
Reverse Recovery Time	Trr	IS=140A , di/dt=100A/us , TJ=25℃	-	98	-	nS
Reverse Recovery Charge	Qrr		-	218	-	nC

Note :


1. The test condition is $V_{DD}=50V$, $V_{GS}=10V$, $L=0.5mH$, $R_G=25\Omega$;




Typical Characteristics




Output Characteristics




Transfer Characteristics




Capacitance Characteristics




Gate Charge




Current dissipation




Power dissipation




$R_{DS(on)}$ VS Drain Current




Forward characteristics of reverse diode




Normalized breakdown voltage



Normalized Threshold voltage





Safe Operation Area





Test Circuit



Gate Charge





Resistive Load Switching Time




Un-clamped Inductive Load Switching



Drain-Source Body Diode Reverse Recovery



Temperature Profile for IR Reflow Soldering



Profile Feature	Sn-Pb Eutectic Assembly	Pb-Free Assembly
Preheat & Soak		
Temperature min (T _{min})	100°C	150°C
Temperature max (T _{max})	150°C	200°C
Time (T _{min} to T _{max}) (t _s)	60-120 seconds	60-120 seconds
Average ramp-up rate (T _{max} to T _p)	3 °C/second max.	3°C/second max.
Liquidous temperature (T _L)	183 °C	217°C
Time at liquidous (t _L)	60-150 seconds	60-150 seconds
Peak package body Temperature e (T _p)*	See Classification Temp in table 1	See Classification Temp in table 2
Time (t _p)** within 5°C of the specified classification temperature (T _c)	20** seconds	30** seconds
Average ramp-down rate (T _p to T _{max})	6 °C/second max.	6 °C/second max.
Time 25°C to peak temperature	6 minutes max.	8 minutes max.
* Tolerance for peak profile Temperature (T _p) is defined as a supplier minimum and a user maximum. ** Tolerance for time at peak profile temperature (t _p) is defined as a supplier minimum and a user maximum		

Table 1. SnPb Eutectic Process – Classification Temperatures (T_c)



Package Thickness	Volume mm ³ <350	Volume mm ³ ≥350
<2.5 mm	235 °C	220 °C
≥2.5 mm	220 °C	220 °C

Table 2. Pb-free Process – Classification Temperatures (T_c)


Package Thickness	Volume mm ³ <350	Volume mm ³ 350-2000	Volume mm ³ >2000
<1.6 mm	260 °C	260 °C	260 °C
1.6 mm – 2.5 mm	260 °C	250 °C	245 °C
≥2.5 mm	250 °C	245 °C	245 °C

TOLL Reel Information

REEL DIMENSIONS



TAPE DIMENSIONS




A0: Dimension designed to accommodate the component width
 B0: Dimension designed to accommodate the component length
 K0: Dimension designed to accommodate the component thickness
 W: Overall width of the carrier tape
 P0: Pitch between successive cavity centers and sprocket hole
 P1: Pitch between successive cavity centers
 P2: Pitch between sprocket hole
 T: Tape material thickness
 D1: Reel Diameter
 W1: Reel Width

DIMENSIONS										(Unit: mm)
Reel	D1	W1								Material
	330	24.4								Hips
Tape	P0	P1	P2	W	A0	B0	K0	T	Pin 1 Quadrant	Material
	2	4	12	24	10.3	12.1	2.6	0.35	Q1	PC

All dimensions are nominal



TOLL Package Information



Symbol	Dimensions In Millimeters		
	Min.	Nom.	Max.
A	2.15	2.30	2.45
b	0.60	0.75	0.90
C	0.40	0.50	0.60
D	10.18	10.38	10.58
D1	3.15	3.3	3.45
E	9.70	9.90	10.10
E1	9.65	9.80	9.95
E2	7.90	--	9.15
E3	7.20	--	8.40
e	1.20 BSC		
F	1.05	1.20	1.35
H	11.45	11.70	11.95
H2	6.75	7.00	7.3
H3	3.00 BSC		
L	1.20	--	2.10
L1	0.50	0.75	0.90
L2	0.45	0.6	0.75
M	0.08 REF.		
β	8°	10°	12°