


1. External Dimensions (Unit:mm)



Type	A	B	C	D Typ.	E Typ.	F Typ.	G Typ.	H Typ.	Q'TY/Reel
AAPS0530	5.25±0.2	5.8Max	3.0Max	2.54	1.02	6.76	2.79	2.95	2000

2. Part Number Code

AAPS	05	30	M	100	D
Series Name	Dimensions: L*W	Dimensions: H	Tolerance ±20%	Inductance	Materials

3. Electrical Characteristics

Part Number	Inductance (μH)	Test Conditions	DC Resistance (mΩ) Max.	Heat Rating Current Irms(A) Typ.	Saturation Current Isat(A) Typ.
AAPS0530M100D	10	100KHz/1V	129.5	2.8	2.35

Notes:

- 1) AEC-Q200 qualified.
- 2) All test data is referenced to 25°C ambient.
- 3) Absolute maximum voltage 60VDC.
- 4) Operating temperature range -55°C to +155°C, (Including self - temperature rise).
- 5) Irms :DC current(A) that will cause an approximate ΔT of 40°C.
- 6) Isat :DC current(A) that will cause I_o to drop approximately 40%.
- 7) The part temperature(ambient + temp rise) should not exceed 155°C under worst case operating conditions. Circuit design and other cooling provisions all affect the part temperature, part temperature should be verified in the end application.