






RoHS Compliant


REV.	ECN NO OR DESCRIPTION	REVISED	DATE



SECTION:A-A



CONNECTOR EDGE
PCB参考图



NOTE:

- MATERIAL SPECIFICATION:
 - HOUSING:HIGH TEMPERATURE RESISTANT PLASTIC,UL94 V-0.
 - CONTACTS:COPPER ALLOY
 - MID PLATE: STAINLESS STEEL
 - FRONT SHELL: STAINLESS STEEL
- PLATING SPECIFICATION:
 - CONTACTS:
Ni 50u" MIN. UNDER PLATED OVER ALL.
Au PLATED ON THE FUNCTIONAL AREA OF CONTACT.
(GOLD PLATING THICKNESS FOLLOW THE P/N)
PLATING SPECIFICATIONS OF THE SOLDER AREA FOLLOW THE P/N
- MECHANICAL PERFORMANCE,
 - INSERTION FORCE: 0.5~2.0kgf.
 - REMOVAL FORCE: 0.8kgf~2.0kgf.
 - DURABILITY: 10000 CYCLES.
- ELECTRICAL PERFORMANCE,
 - CURRENT RATING:3.0A
VOLTAGE RATING:5.0V
 - LLCR:
VBUS & GND PINS AND OTHER PINS: 40m*/PIN MAX.
SHIELD: 50m*/MAX.
LLCR MAX. CHANGE OF ALL PINS: 10m*.
 - INSULATION RESISTANCE: 100M* MIN
 - DIELECTRIC WITHSTAND VOLTAGE,AC 100V FOR 1 MINUTE.
- ENVIRONMENTAL PERFORMANCE:
OPERATING TEMPERATURE: -25~C~+85~C.
- IR REFLOW:
THE PEAK TEMPERATURE ON THE BOARD SHALL
BE MAINTAINED FOR 10 SECONDS AT 260°C.

USB TYPE C PIN ASSIGNMENTS											
A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
					CC1	DP1	DN1				
GND			VBUS					CC2	VBUS		GND
B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1

MEASURE POINT:
QUADRANT POINT
TANGENCY POINT
INTERSECTION POINT



UNLESS OTHERWISE
SPECIFIED,TOLERANCE:
X. ±0.25
X.x ±0.20
X.xx ±0.15
ANGULAR ±3°



联晟欣连接器（深圳）有限公司
Lianshengxin Connector (Shenzhen) Co., Ltd

DESIGN	Andy	DATE	2014.12.24	TITLE:	TYPE C 8PIN带铜片L=6.8后两脚插件无弹1.0脚长		
CHECKED		DATE		REV: 04	SCALE: 1:1	UNIT: mm	
APPROVED		DATE		DRAWING NO:	SIZE: A4	SHEET: 1/1	