


Transient Voltage Suppressors for ESD Protection

SE05D5V11GY

Features

- ◆ Protects one I/O line
- ◆ Low clamping voltage
- ◆ Working voltage: 5V
- ◆ Low leakage current


SOD-523



Applications

- ◆ Cellular Handsets and Accessories
- ◆ Portable Electronics
- ◆ Servers, Notebook, and Desktop PC
- ◆ Display Portst

Functional Diagram



Mechanical Characteristics

- ◆ SOD-523 Package
- ◆ Molding Compound Flammability Rating: UL 94V-0
- ◆ Quantity Per Reel: 3,000pcs
- ◆ Reel Size: 7 inch

Absolute Maximum Rating

Symbol	Parameter	Value	Units
T _L	Lead Soldering Temperature	260 (10sec)	°C
T _{STG}	Storage Temperature Range	-55 to +150	°C
T _{OP}	Operating Temperature Range	-55 to +150	°C
	Air Discharge IEC61000-4-2 (ESD)	±30	KV
	Contact Discharge	±30	
	IEC61000-4-4 (EFT)	40	A

Transient Voltage Suppressors for ESD Protection

SE05D5V11GY

Electrical Characteristics (@T_A=25°C, unless otherwise specified)

Symbol	Symbol	Conditions	Min.	Typ.	Max.	Units
Reverse Stand-off Voltage	V_{RWM}	--	--	--	5.0	V
Reverse Breakdown Voltage	V_{BR}	$I_T = 1mA$	6.0	--	--	V
Reverse Leakage Current	I_R	$V_{RWM}=5V$	--	--	0.1	μA
Clamping Voltage	V_C	$I_{PP}=1A, t_p=8/20\mu s$	--	8.0	--	V
		$I_{PP}=10A, t_p=8/20\mu s$	--	11.0	--	V
Junction Capacitance	C_J	$V_R=0V, f=1MHz$	--	70.0	--	pF

Characteristic Curves

Fig1. V-I Curve Characteristics (Ui-directional)




Fig2. Pulse Waveform (8/20μs)




Fig3. Pulse Derating Curve






Fig4. ESD Clamping (30kV Contact)



Transient Voltage Suppressors for ESD Protection

SE05D5V11GY

SOD-523 Package Outline & Dimensions



Symbol	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	0.51	0.77	0.020	0.031
A1	0.40	0.70	0.015	0.028
b	0.25	0.35	0.010	0.014
c	0.08	0.15	0.003	0.006
D	0.75	0.85	0.030	0.033
E	1.10	1.30	0.043	0.051
E1	1.50	1.70	0.059	0.067
E2	0.20 REF		0.008 REF	
L	0.01	0.07	0.001	0.003
θ	7° REF		7° REF	

Warning



- ◆ SOCAY owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property.
- ◆ SOCAY reserves the right to make changes without further notice to any products herein.
- ◆ SOCAY makes no warranties, representations or warranties as to the fitness of its products for any particular purpose, and disclaims any liability.
- ◆ The parameters provided in the SOCAY datasheet specification may vary from application to application, and the actual performance may vary over time. All operating parameters must be verified by the customer's technical expert before application.
- ◆ Any and all responsibilities and liabilities are disclaimed if any item under this notice of warning is not complied with.