


Transient Voltage Suppressors for ESD Protection

SE05T1D32GZ

Features

- ◆ Working voltage: 5V
- ◆ Low capacitance: 0.7pF (Typical)
- ◆ Low leakage current: 1μA @ V_{RWM}
- ◆ Low clamping voltage
- ◆ Response Time is < 1 ns


SOT-143



Applications

- ◆ Fire Wire & USB
- ◆ Sensitive Analog Inputs
- ◆ Notebook Computers
- ◆ Portable Electronics

Pin Configuration



Mechanical Characteristics

- ◆ SOT-143 Package
- ◆ Molding Compound Flammability Rating: UL 94V-0
- ◆ Quantity Per Reel: 3,000pcs
- ◆ Reel Size: 7 inch

Absolute Maximum Rating


Symbol	Parameter	Value	Units
T_{LST}	Lead Soldering Temperature	260 (10sec)	°C
T_{STG}	Storage Temperature Range	-55 to +150	°C
T_{OPT}	Operating Temperature Range	-55 to +150	°C
V_{ESD}	ESD per IEC 61000-4-2(Air)	±30	KV
	ESD per IEC 61000-4-2 (Contact)	±30	

Transient Voltage Suppressors for ESD Protection

SE05T1D32GZ

I-V Curve Characteristics

Symbol	Parameter
I_{PP}	Maximum Reverse Peak Pulse Current
V_C	Clamping Voltage @ I_{PP}
V_{RWM}	Working Peak Reverse Voltage
I_R	Maximum Reverse Leakage Current @ V_{RWM}
V_{BR}	Breakdown Voltage @ I_T
I_T	Test Current
I_F	Forward Current
V_F	Forward Voltage @ I_F



Electrical Characteristics (@ $T_A=25^\circ\text{C}$ unless Otherwise Specified)

Symbol	Test Condition	Minimum	Typical	Maximum	Units
V_{RWM}	Any I/O pin to GND	--	--	5	V
I_R	$V_{RWM}=5\text{V}, T=25^\circ\text{C}$ Any I/O pin to GND	--	--	1	μA
V_{BR}	$I_T=1\text{mA}$ Any I/O pin to GND	6	--	9	V
V_C	$I_{PP}=1\text{A}, t_p=8/20\mu\text{s}$ Any I/O pin to GND	--	10	--	V
V_C	$I_{PP}=5\text{A}, t_p=8/20\mu\text{s}$ Any I/O pin to GND	--	13	--	V
C_J	$V_R=0\text{V}, f=1\text{MHz}$ Any I/O pin to GND	--	0.7	--	pF

Transient Voltage Suppressors for ESD Protection

SE05T1D32GZ

Characteristics Curves ($T_A=25^{\circ}\text{C}$ unless otherwise noted)

Fig1. Pulse Waveform




Fig2. Pulse Derating Curve






Fig3. ESD Clamping (8KV Contact)



Transient Voltage Suppressors for ESD Protection


SE05T1D32GZ

SOT-143 Package Outline & Dimensions



Symbol	Inches			Millimeters		
	Min	Nom	Max	Min	Nom	Max
A	0.031	--	0.048	0.80	--	1.22
A1	0.000	--	0.008	0.013	--	0.15
A2	0.020	0.035	0.042	0.75	0.90	1.07
b	0.011	--	0.020	0.30	--	0.51
b1	0.029	--	0.037	0.76	--	0.94
c	0.003	--	0.008	0.08	--	0.20
D	0.110	0.114	0.120	2.80	2.90	3.04
E	0.082	0.093	0.104	2.10	2.37	2.64
E1	0.047	0.051	0.055	1.20	1.30	1.40
e	0.075			1.92 BSC		
e1	0.008			0.20 BSC		
L	0.015	0.020	0.024	0.40	0.50	0.60
L1	(0.021)			(0.54)		
N	4			4		
θ	0°	--	8°	0°	--	8°
aaa	0.006			0.15		
bbb	0.008			0.20		
ccc	0.004			0.10		

Soldering Footprint



Symbol	Inches	Millimeters
C	(0.087)	(2.20)
E1	0.076	1.92
E2	0.068	1.72
G	0.031	0.80
X1	0.039	1.00
X2	0.047	1.20
Y	0.055	1.40
Z	0.141	3.60

Transient Voltage Suppressors for ESD Protection

SE05T1D32GZ

Warning



- ◆ SOCAY owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property.
- ◆ SOCAY reserves the right to make changes without further notice to any products herein.
- ◆ SOCAY makes no warranties, representations or warranties as to the fitness of its products for any particular purpose, and disclaims any liability.
- ◆ The parameters provided in the SOCAY datasheet specification may vary from application to application, and the actual performance may vary over time. All operating parameters must be verified by the customer's technical expert before application.
- ◆ Any and all responsibilities and liabilities are disclaimed if any item under this notice of warning is not complied with.