


修 订	标 记	修 改 描 要	签 名	日 期
REV A0		NEW DWG		2016-03-12

- 规格说明:Specifications:
- 电气特性:Electrical:
- 1. 额定电流: Current Rating
1.5A/contact terminal
 - 2. 额定电压: Voltage Rating
30V DC
 - 3. 接触阻抗:Contact Resistance
30 milliohms MAX
 - 4. 耐电压:Dielectnic Withstanding Voitage:
500 V AC AT Sea Levol
 - 5. 绝缘阻抗:Lnsulation Resistance:
1000MEGA ohms MIN
- 物理性能:Mechanical:
- 1. 插拔力: Cnnector Mate and Unmate Force
Mate force:3.57kgf (MAX)
Unmate force:1.02kgf (MIN)
 - 2. 端子保持力: Terminal Retenion
1.2kgf (MIN)
- 原材料:Matorial:
- 1. 塑胶:Housing:
Hing Temperature Ternerplastics,
U1 94V-0 LCP White/Black
 - 2. 端子>Contact:Copper Alloy C5191
 - 3. 外壳:Shell: Copper Alloy SUS304
- 电镀:Finish:
- 1. 端子>Contact: Piated Gold in Mating Area;
半 金 锡 1U
 - 2. 外壳:Shell:
Nickel Plating



		深圳市华德共创科技有限公司 Shenzhen Huade co-create Technology Co.,LTD 电话：0755-27111216 传真：0755-29940187						
-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表			 		TITLE: MICRO四脚短脚平口铜壳镀锡无柱 产品名称: 针长1.5			
X.X	±0.30	X.X*	±3°	APPD: 核准:	PART NO: 产品编号: MICRO-ZL-103PWB			
X.XX	±0.20	X.XX*	±2°	CHECK: 校对: 王建业	DATE	SCALE	UNIT	CODE NUMBER
X.XXX	±0.10	X.XXX*	±1°	DRAW: 绘图: 黄艳兰	2016-03-12	1:1	mm	A001