




修 订	标 记	修 改 描 要	签 名	日 期
REV NO		REVISION DESCRIPTION	SIGNATURE	DATE
		NEW DRG		2016-03-12




Note:  
 1.Material  
 1.1: Housing: Thermoplastic,High temp, UL94-V0;  
 1.2: Actuator: Thermoplastic,High temp, UL94-V0;  
 1.3: Contact: Phosphor Bronze.  
 1.4: LEG: Phosphor Bronze.  
 2.Plating  
 2.1: Contact: Matte Tin Or Gold Plating Nickel Overall .  
 2.2: LEG: Matte Tin Plating Over Nickel.  
 3.Part NO:



Number of Contacts	Dimension		
	A	B	C
4	6.80	1.50	4.10
5	7.30	2.00	4.60
6	7.80	2.50	5.10
7	8.30	3.00	5.60
8	8.80	3.50	6.10
9	9.30	4.00	6.60
10	9.80	4.50	7.10
11	10.30	5.00	7.60
12	10.80	5.50	8.10
13	11.30	6.00	8.60
14	11.80	6.50	9.10
15	12.30	7.00	9.60
16	12.80	7.50	10.10
17	13.30	8.00	10.60
18	13.80	8.50	11.10
19	14.30	9.00	11.60
20	14.80	9.50	12.10
21	15.30	10.00	12.60
22	15.80	10.50	13.10
23	16.30	11.00	13.60
24	16.80	11.50	14.10
25	17.30	12.00	14.60
26	17.80	12.50	15.10
27	18.30	13.00	15.60
28	18.80	13.50	16.10
29	19.30	14.00	16.60
30	19.80	14.50	17.10
31	20.30	15.00	17.60
32	20.80	15.50	18.10
n	6.80+(n-4)*0.5	1.50+(n-4)*0.5	4.10+(n-4)*0.5



FPC/FFC Insert Direction  
 Recommended P.C.B Layout



Recommended FPC Dimension



深圳市华德共创科技有限公司  
 Shenzhen Huade co-create Technology Co.,LTD  
 电话: 0755-27111216 传真: 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表		 	TITLE: 产品名称: FPC 0.5间距2.0高带蝴蝶扣掀盖式			
X.X ±0.30	X.X* ±3°	APPD: 核准:	PART NO: 产品编号: 0.5K-2.0DK-nPWB			
X.XX ±0.20	X.XX* ±2°	CHECK: 校对: 王建业	DATE	SCALE	UNIT	CODE NUMBER
X.XXX ±0.10	X.XXX* ±1°	DRAW: 绘图: 黄艳兰	2016-03-12	1:1	mm	A001