






修 订 REV NO	标 记 MARK	修 改 描 要 REVISION DESCRIPTION	签 名 SIGNATURE	日 期 DATE
		NEW DWG		2016-03-12



RECOMMEND P.C.B LAYOUT
TOP VIEW TOLERANCE:±0.05



NOTES:

* MATERIAL:

- 1.HOUSING:LCP+30%G/F,UL94 V-0,Color:Black;
- 2.CONTACT: Brass, T=0.40mm;
- 3.Shell: STAINLESS STEEL, T=0.20mm.



* FINISH:

1.CONTACT:

GOLD PLATED ALL OVER;
NICKEL UNDER PLATED ALL OVER.

2.Shell:

Ni UNDER PLATED OVER ALL;
Matte Tin Plated Over All.



深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co.,LTD

电话: 0755-27111216 传真: 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表				TITLE: 产品名称: 唐虞1.5卧贴针座		PART NO: 产品编号: HDGC1507WR-S-6P			
X.X	±0.30	X.X*	±3°	APPD: 核准:		DATE	SCALE	UNIT	CODE NUMBER
X.XX	±0.20	X.XX*	±2°	CHECK: 校对: 王建业		2016-03-12	1:1	mm	A001
X.XXX	±0.10	X.XXX*	±1°	DRAW: 绘图: 黄艳兰					