

STK615N4F8AG

Datasheet

Automotive N-channel 40 V, 0.48 mΩ max., 672 A STripFET F8 Power MOSFET in a PowerLeaded 8x8 package



PowerLeaded 8x8



Features

Order code	V_{DS}	$R_{DS(on)}$ max.	I_D
STK615N4F8AG	40 V	0.48 mΩ at 10 V	672 A

- AEC-Q101 qualified
- MSL1 grade
- 175 °C maximum operating junction temperature
- 100% avalanche tested
- Low gate charge Q_g

Applications

- Automotive motor control
- Body and convenience
- Chassis and safety
- Power train for ICE

Description

The STK615N4F8AG is a 40 V N-channel enhancement mode Power MOSFET designed in STripFET F8 technology featuring an enhanced trench gate structure.

It ensures a state-of-the-art of figure of merit for very low on-state resistance while reducing internal capacitances and gate charge for faster and more efficient switching.

Product status link
STK615N4F8AG

Product summary	
Order code	STK615N4F8AG
Marking(1)	615N4F8
Package	PowerLeaded 8x8
Packing	Tape and reel

1. *Engineering samples are clearly identified with a dedicated special symbol in the marking of each unit.*

1 Electrical ratings

Table 1. Absolute maximum ratings (at T_C = 25 °C unless otherwise specified)

Symbol	Parameter	Value	Unit
V_{DS}	Drain-source voltage	40	V
V_{GS}	Gate-source voltage	±20	V
I_D[1]	Drain current (continuous) at T_C = 25 °C[2]	672	A
	Drain current (continuous) at T_C = 100 °C[2]	475	
	Drain current (continuous) at T_C = 25 °C[3]	200	
I_{DM}[1][2][4]	Drain current (pulsed), t_p = 10 µs	2688	A
P_{TOT}	Total power dissipation at T_C = 25 °C	390	W
I_{AS}	Single pulse avalanche current (pulse width limited by T_J max.)	90	A
E_{AS}	Single pulse avalanche energy (starting T_J = 25 °C, I_D = 90 A, R_{Gmin} = 25 Ω)	1779	mJ
T_J	Operating junction temperature range	-55 to 175	°C
T_{stg}	Storage temperature range		°C

1. *Specified by design, not tested in production.*
2. *This is the theoretical current value only related to the silicon.*
3. *This current value is limited by package.*
4. *Pulse width is limited by safe operating area.*

Table 2. Thermal data

Symbol	Parameter	Value	Unit
R_{thJA}[1]	Thermal resistance, junction-to-ambient (on 2s2p FR-4 board vertical in still area)	13.8	°C/W
R_{thJC}	Thermal resistance, junction-to-case	0.39	°C/W

1. *Defined according to JEDEC standards (JESD51-5, -7).*

2 Electrical characteristics

T_J = 25 °C unless otherwise specified.

Table 3. On/off states

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
$V_{(BR)DSS}$	Drain-source breakdown voltage	V_{GS} = 0 V, I_D = 1 mA	40	-	-	V
I_{DSS}	Zero gate voltage drain current	V_{DS} = 40 V, V_{GS} = 0 V	-	-	1	µA
		V_{DS} = 40 V, V_{GS} = 0 V, T_J = 125°C(1)	-	-	100	
I_{GSS}	Gate-body leakage current	V_{GS} = 20 V, V_{DS} = 0 V	-	-	100	nA
$V_{GS(th)}$	Gate threshold voltage	V_{DS} = V_{GS}, I_D = 250 µA	2	-	4	V
$R_{DS(on)}$	Static drain-source on-resistance	V_{GS} = 10 V, I_D = 90 A	-	0.35	0.48	mΩ

1. *Specified by design and evaluated by characterization, not tested in production.*

Table 4. Dynamic

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
C_{iss}(1)	Input capacitance	V_{DS} = 25 V, f = 1 MHz, V_{GS} = 0 V	-	13000	-	pF
C_{oss}(1)	Output capacitance		-	3400	-	pF
C_{rss}(1)	Reverse transfer capacitance		-	85	-	pF
Q_g(1)	Total gate charge	V_{DD} = 20 V, I_D = 180 A, V_{GS} = 0 to 10 V	-	162	-	nC
Q_{gs}(1)	Gate-source charge		-	62	-	nC
Q_{gd}(1)	Gate-drain charge		-	20	-	nC

1. *Specified by design and evaluated by characterization, not tested in production.*

Table 5. Switching times

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
$t_{d(on)}$(1)	Turn-on delay time	V_{DD} = 20 V, I_D = 90 A, R_G = 4.7 Ω, V_{GS} = 10 V	-	36	-	ns
t_r(1)	Rise time		-	21	-	ns
$t_{d(off)}$(1)	Turn-off delay time		-	93	-	ns
t_f(1)	Fall time		-	30	-	ns

1. *Specified by design and evaluated by characterization, not tested in production.*

Table 6. Source-drain diode

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
I_{SD}(1)	Forward on current (continuous)	T_C = 25 °C	-		240	A
V_{SD}	Forward on voltage	I_{SD} = 90 A, V_{GS} = 0 V	-		1.1	V
t_{rr}(1)	Reverse recovery time	I_D = 90 A, di/dt = 100 A/µs, V_{DD} = 32 V	-	84		ns
Q_{rr}(1)	Reverse recovery charge		-	143		nC
I_{RRM}(1)	Reverse recovery current		-	3.4		A

1. *Specified by design and evaluated by characterization, not tested in production.*

2.1 Electrical characteristics (curves)

Figure 1. Total power dissipation




Figure 2. Drain current vs case temperature




Figure 3. Safe operating area




Figure 4. Normalized transient thermal impedance




Figure 5. Typical output characteristics




Figure 6. Typical transfer characteristics




Figure 7. Typical on-resistance vs gate-source voltage




Figure 8. Typical gate charge characteristics




Figure 9. Typical capacitance characteristics




Figure 10. Avalanche characteristics




Figure 11. Avalanche energy




Figure 12. Typical drain-source on-resistance




Figure 13. Normalized gate threshold voltage vs temperature




Figure 14. Typical reverse diode forward characteristics




Figure 15. Normalized $V_{(BR)DSS}$ vs temperature





Figure 16. Normalized on-resistance vs temperature




3 Package information

To meet environmental requirements, ST offers these devices in different grades of ECOPACK packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions, and product status are available at: www.st.com. ECOPACK is an ST trademark.


3.1 PowerLeaded 8x8 package information

Figure 17. PowerLeaded 8x8 package outline



DM00548355_Rev_4

Figure 18. **Section details**




PowerLeaded_8x8_DM00548355_details

Table 7. **PowerLeaded 8x8 mechanical data**

Dim.	mm		
	Min.	Typ.	Max.
A			1.85
A1	0.00	0.08	0.15
A2	1.50	1.60	1.70
A3	0.60	0.70	0.80
b	0.90	1.00	1.10
c	0.20		0.25
c1	0.19	0.20	0.21
c2	0.49		0.56
c3	0.48	0.50	0.52
D	6.10	6.20	6.30
D1	4.75	4.90	5.05
D2	3.50	3.65	3.80
D3	0.65	0.75	0.85
D4			0.20
D5	2.90	3.10	3.30
E	7.90	8.00	8.10
E1	6.95	7.10	7.25
E2	6.70	6.80	6.90
E3	2.50	2.60	2.70
E4	0.65	0.80	0.95
E5	1.50	1.70	1.90
e	1.90	2.00	2.10
H	7.85	8.00	8.15
K	0.45	0.55	0.65
K1	1.75	1.90	2.05
L	1.00	1.20	1.30
L1	0.60	0.70	0.80
L2	0.23BSC		
R	0.20REF		
Θ	0°		8°
Θ1	6°	10°	14°


Figure 19. **PowerLeaded 8x8 recommended footprint (dimensions are in mm)**



PowerLeaded_8x8_DM00548355_footprint

3.1.1 PowerLeaded 8x8 marking information

Figure 20. **PowerLeaded 8x8 marking information**



Note: Engineering Samples: these samples can be clearly identified by a dedicated special symbol in the marking of each unit. These samples are intended to be used for electrical compatibility evaluation only; usage for any other purpose may be agreed only upon written authorization by ST. ST is not liable for any customer usage in production and/or in reliability qualification trials.

Commercial Samples: fully qualified parts from ST standard production with no usage restrictions.

Revision history

Table 8. **Document revision history**

Date	Revision	Changes
17-Jan-2023	1	Initial release.
16-Oct-2024	2	Modified title, *Features*, *Applications* and *Description*. Added schematic on cover page. Modified *Section 1: Electrical ratings*, *Section 2: Electrical characteristics*. Added *Section 2.1: Electrical characteristics (curves)*. Added *Section 3.1.1: PowerLeaded 8x8 marking information*. Minor text changes
08-Nov-2024	3	Document classification changed from ST restricted to public. Modified *Figure 3. Safe operating area* and *Figure 7. Typical on-resistance vs gate-source voltage*.
09-Jan-2025	4	Updated *Figure 6. Typical transfer characteristics*. Minor text changes.
14-Mar-2025	5	Updated *Figure 6. Typical transfer characteristics*.
17-Dec-2025	6	Updated Figure 6. Typical transfer characteristics.

Contents

1 **Electrical ratings** 2
2 **Electrical characteristics** 3
2.1 Electrical characteristics (curves) 5
3 **Package information** 8
3.1 PowerLeaded 8x8 package information 8
3.1.1 PowerLeaded 8x8 marking information 12
Revision history 13

IMPORTANT NOTICE – READ CAREFULLY

STMicroelectronics NV and its subsidiaries (“ST”) reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice.

In the event of any conflict between the provisions of this document and the provisions of any contractual arrangement in force between the purchasers and ST, the provisions of such contractual arrangement shall prevail.

The purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST’s terms and conditions of sale in place at the time of order acknowledgment.

The purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of the purchasers’ products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

If the purchasers identify an ST product that meets their functional and performance requirements but that is not designated for the purchasers' market segment, the purchasers shall contact ST for more information.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2025 STMicroelectronics – All rights reserved