




SS-22F32-GXXX

SS: Straight shank


G-Switch P/N

Switch Height(mm)

G020=2.0 G030=3.0
G040=4.0 G050=5.0
G055=5.5 G060=6.0
G065=6.5 G070=7.0
G075=7.5 G080=8.0
G085=8.5 G090=9.0
G095=9.5 G100=10.0



RECOMMENDED PCB LAYOUT
TOLERANCE: ± 0.05



CIRCUIT DIAGRAM

G-Switch Specification:

1. Operating temperature range: $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$
2. Rating: 0.5mA.50V DC
3. Insulation resistance: 100M Ω min. 100V DC
4. Dielectric strength: 500V AC for 1 min
5. Contact resistance: 100m Ω max.
6. Terminals arrangement: 2P3T
7. Travel: $3.2 \pm 0.1\text{mm}$
8. Switch lifetime: 10,000Cycles

6	SPRING	STEEL WIRE	NATURAL
5	CONTACT	BRASS STRIP	Ag PLATED
4	TERMINAL	BRASS STRIP	Ag PLATED
3	BASE	PHENOLIC RESIN	NATURAL
2	FRAME	STEEL STRIP	NI PLATED
1	KNOB	PA66	BLACK
NO.	PART NAME	MATERIAL	REMARK



SCALE: 1:1	UNIT: mm	Title: Vertical Slide Switch DIP 23.2×7.5×H7.0mm				 品赞科技 www.dg-switch.com ®	
SIZE: A4		Molde Code: SS-22F32-GXXX					
Unless otherwise General Tolerance:		DRAWN	CHECKED	APPROVED	DATE		
WITHIN 1.5: ±0.10 OVER 1.5: ±0.20 X° ±5°		Jiang	Xia	Chen	2024.11.21	REV: A0	SHEET: 1/1