




■ Specifications

- Voltage rating: 250V AC / DC
- Current rating: 5A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: $\geq 1000\text{M}\Omega$
- Contact resistance: $\leq 10\text{m}\Omega$
- After environmental testing : $\leq 20\text{m}\Omega$

X3025WRS-2x04C-LPSW

01 02 03 04 05 06 07 08 09

① Series No.

02) Category : W-waf er

03) Welding Board Angle: R-90°

④ Welding Way: S-SMT

05) Row No -Pin No : 2*XX-Double row

06 Special N0.: C-The harpoon

⑥7 Material: L B L CB 04V 0

⑦ Material : LP-LCP 94V-0
NO. BACC 04V-0

☀ Planting Category:

⑧ **Flaming Category:**
SN-Bright tin plate

SW Egg Tin plating

SW-Fog Tin plating

⑨ Color :

Blank-natural color

Poles	Dimensions(mm)		
	A	B	C
2*01	6.65	—	4.20
2*02	9.65	3.00	7.20
2*03	12.65	6.00	10.20
2*04	15.65	9.00	13.20
2*05	18.65	12.00	16.20
2*06	21.65	15.00	19.20
2*07	24.65	18.00	22.20
2*08	27.65	21.00	25.20
2*09	30.65	24.00	28.20
2*10	33.65	27.00	31.20
2*11	36.65	30.00	34.20
2*22	39.65	33.00	37.20

	X3025WRS-2x04C-LPSW	LCP UL 94V-0	Brass	Ni:50u"Min; Sn:120u"Min;	Brass	Matte Tin Plating	X3025H
	X3025WRS-2x04C-LPSW					Tin-Plated	
	X3025WRS-2x04C-N0SN	PA66 UL 94V- 0					
	PART NO	Material	Material (Pin)	Finish(Pin)	Material (Solder Tabs)	Finish (Solder Tabs)	

							DSND		DATE		SCALE: N/A	MODEL TYPE: 3.00 mm Crimp Style Connectors
				XKB	ANGLAR	$\pm 5^\circ$	DWN		DATE		VIEW: 	PART NO.: X3025WRS-2x04C-LPSW
Δx					$L \leq 4$	± 0.2	CHKD		DATE		UNIT: mm/in	DWG NO.: X-X3025WRS-2x04C-LPSW
Δx					$4 < L \leq 16$	± 0.3	APPD		DATE		SIZE: A4	
Δx					$16 < L \leq 63$	± 0.4						
MARK	DESCRIPTION			DATE	REVISED	APPROVED						
REVISIONS						UNSPECIFIED TOLERANCES		XKB INDUSTRIAL PRECISION CO.,LIMITED				
www.helloxkb.com								WEIGHT 1.0g				
								SHEET 1/1				
								REVISION A0				