


CRYSTAL UNITS

ACTUAL SIZE: ☐

CXA-016000-2FHE40

CERAMIC PACKAGE



APPLICATIONS

- ▶ DVR
- ▶ Camera
- ▶ Medical
- ▶ Industry Control
- ▶ Wireless
- ▶ Communication
- ▶ Telecom
- ▶ IoT

FEATURES

- ▶ Seam Seal
- ▶ Excellent Solderability
- ▶ Excellent Vibration Resistance & Shock Resistance
- ▶ High Frequency Stability
- ▶ Excellent Thermal Hysteresis
- ▶ RoHS Compliant

Specification

MODEL

DIMENSION	(mm)	2.50 X 2.00
-----------	--------	-------------

FREQUENCY

FREQUENCY RANGE (Fundamental)	MHz	12.000 ~ 66.999
FREQUENCY RANGE (3rd Overtone)	MHz	67.000 ~ 133.000
FREQUENCY TOLERANCE (25°C)	ppm	± 10 ~ ± 50
FREQUENCY STABILITY (Ref to 25°C)	ppm	± 10 ~ ± 100 ± 50 ~ ± 100

ENVIRONMENTAL CONDITION

OPERATING TEMPERATURE RANGE	°C	- 20 ~ + 70 Or Specify (- 40 ~ + 125 is available)	- 55 ~ + 125
STORAGE TEMPERATURE RANGE	°C	- 55 ~ + 125	
AGING / YEAR	ppm	± 3	

ELECTRICAL SPECIFICATIONS

TEST CIRCUIT		S&A 250B With π Fixture
LOAD CAPACITANCE	pF	SERIES, 6pF to 47pF, or Specify
DRIVE LEVEL	uW	15, 30, 50, 100, 200 or special requirement
EQUIVALENT SERIES RESISTANCE	Ω	See Table
SHUNT CAPACITANCE	pF	2.0 Max.

*Specification subject to change without notice.

Equivalent Series Resistance (Ω)

Frequency Range	Mode of Operation	ESR
12.000 ~ 15.999	Fundamental	150 Ω Max.
16.000 ~ 19.999	Fundamental	80 Ω Max.
20.000 ~ 24.999	Fundamental	60 Ω Max.
25.000 ~ 29.999	Fundamental	50 Ω Max.
30.000 ~ 34.999	Fundamental	45 Ω Max.
35.000 ~ 66.999	Fundamental	40 Ω Max.
67.000 ~ 133.000	3rd Overtone	100 Ω Max.

Dimension(mm)

