ACCURATE KINETIC ENERGY

CRYSTAL UNITS

ACTUAL SIZE: ▭

CXA-037400-AF6F20 CERAMIC PACKAGE



APPLICATIONS

- DVR
- Camera
- Medical
- Industry Control
- Wireless
- Communication
- Telecom
- IoT

FEATURES

- Seam Seal
- Excellent Solderability
- Excellent Vibration Resistance & Shock Resistance
- High Frequency Stability
- Excellent Thermal Hysteresis
- RoHS Compliant

Specification

MODEL			
DIMENSION	**(mm)**	2.00 X 1.60	
FREQUENCY			
FREQUENCY RANGE (Fundamental)	**MHz**	16.000 ~ 96.000	
FREQUENCY RANGE (3rd Overtone)	**MHz**	100.000 ~ 125.000	
FREQUENCY TOLERANCE (25°C)	**ppm**	± 10 ~ ±100	
FREQUENCY STABILITY (Ref to 25°C)	**ppm**	± 15 ~ ± 100	± 50 ~ ± 100
ENVIRONMENTAL CONDITION			
OPERATING TEMPERATURE RANGE	**°C**	- 20 ~ + 70 Or Specify (- 40 ~ + 125 is available)	- 55 ~ + 125
STORAGE TEMPERATURE RANGE	**°C**	- 55 ~ + 125	
AGING / YEAR	**ppm**	± 3	
ELECTRICAL SPECIFICATIONS			
TEST CIRCUIT		S&A 250B With π Fixture	
LOAD CAPACITANCE	**pF**	SERIES, 6pF to 47pF, or Specify	
DRIVE LEVEL	**uW**	15, 30, 50, 100, 200 or special requirement	
EQUIVALENT SERIES RESISTANCE	**Ω**	See Table	
SHUNT CAPACITANCE	**pF**	2.0 Max.	

*Specification subject to change without notice.

Equivalent Series Resistance (Ω)

Frequency Range	Mode of Operation	ESR
16.000 ~ 19.199	Fundamental	150Ω Max.
19.200 ~ 21.999	Fundamental	100Ω Max.
22.000 ~ 35.999	Fundamental	80Ω Max.
36.000 ~ 96.000	Fundamental	60Ω Max.
100.000 ~ 125.000	3rd Overtone	120Ω Max.

Dimension(mm)