




A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SD2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SD1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

SPECIFICATIONS:

1. ELECTRICAL CHARACTERISTICS:

- 1-1. CONTACT RESISTANCE: 30m Ω MAX.
- 1-2. DIELECTRIC WITHSTANDING VOLTAGE: 100V AC FOR ONE MINUTE.
- 1-3. INSULATION RESISTANCE: 100M Ω MIN. MEASURED BY 500 VDC

2. MECHANICAL CHARACTERISTICS:

- 2-1. INSERTION FORCE :0.5-2.0Kgf (REF.)
- 2-2. WITHDRAWAL FORCE :0.8-2.0Kgf (REF.)

3. LIFE TEST: 10,000 CYCLES.



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X" ±0.5"	DRAWN BY :	DATE :	PART NAME:
	陈一鸣	2014-02-23	USB TYPE C 母座16P 立贴10.0H
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	CHECKED BY:	DATE :	PART NO.
	马跃	2014-02-23	HYCW721-USBC16-100B
	APPROVED BY:	DATE :	DRAW NO:
	邱敏	2014-02-23	HYC-2605291604
			SHEET NO.
			1 OF 1

RECOMMENDED P.C.B. LAYOUT (T:1.00mm)
TOLERANCE UNSPECIFIED ±0.05mm