




		D		E	
REV.	DESCRIPTION	ECN NO.	NAME	DATE	



Part No	PIN	A	B	C	D
AFE-MX1.25-2PWT-W1	2	1.25	0.00	4.40	7.50
AFE-MX1.25-3PWT-W1	3	2.50	0.00	5.65	8.75
AFE-MX1.25-4PWT-W1	4	3.75	2.50	6.90	10.00
AFE-MX1.25-5PWT-W1	5	5.00	3.75	8.15	11.25
AFE-MX1.25-6PWT-W1	6	6.25	5.00	9.40	12.50
AFE-MX1.25-7PWT-W1	7	7.50	6.25	10.65	13.75
AFE-MX1.25-8PWT-W1	8	8.75	7.50	11.90	15.00
AFE-MX1.25-9PWT-W1	9	10.00	8.75	13.15	16.25
AFE-MX1.25-10PWT-W1	10	11.25	10.00	14.40	17.50
AFE-MX1.25-11PWT-W1	11	12.50	11.25	15.65	18.75
AFE-MX1.25-12PWT-W1	12	13.75	12.50	16.90	20.00
AFE-MX1.25-13PWT-W1	13	15.00	13.75	18.15	21.25
AFE-MX1.25-14PWT-W1	14	16.25	15.00	19.40	22.50
AFE-MX1.25-15PWT-W1	15	17.50	16.25	20.65	23.75
AFE-MX1.25-16PWT-W1	16	18.75	17.50	21.90	25.00

1. 极数 Number of poles: 2-16
2. 工作温度 Working Temperature: -40°C - $+85^{\circ}\text{C}$
3. 额定电压 Voltage rating : 125V AC
4. 额定电流 Rated current : 1A
4. 接触电阻 Contact resistance: $\leq 30\text{m}\Omega$
5. 绝缘电阻 Insulation resistance: $\geq 100\text{M}\Omega$
6. 耐压 Withstand voltage : 250V AC
7. 端子 Terminal : 黄铜 Brass
8. 外壳 Housing : LCP

PCB.焊接图
PCB.WELDING DRAWING

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				BXCONN [®]	
DIM. TOL. x0~2c ±0.20 x2~5c ±0.30 x5 ±0.50 GENERAL ANGLE: ±0.5°		TITLE: WAFER 1.25 卧贴					
		DWG. NO.: AFE-MX1.25-NPWT-W1		CHECKED: MAX			
		PART NO.: AFE-MX1.25-NPWT-W1		DRAWN: ELLA			
		UNIT: mm	SCALE: none	SHEET: 1 of 1	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL

