





REV.	DESCRIPTION	ECN NO.	NAME	DATE

P/N	PIN	DIM.A	DIM.B
AM-PM1.0-V13-2*1P	2*1	0.00	1.00
AM-PM1.0-V13-2*2P	2*2	1.00	2.00
AM-PM1.0-V13-2*3P	2*3	2.00	3.00
AM-PM1.0-V13-2*4P	2*4	3.00	4.00
AM-PM1.0-V13-2*5P	2*5	4.00	5.00
AM-PM1.0-V13-2*6P	2*6	5.00	6.00
AM-PM1.0-V13-2*7P	2*7	6.00	7.00
AM-PM1.0-V13-2*8P	2*8	7.00	8.00
AM-PM1.0-V13-2*9P	2*9	8.00	9.00
.....			
AM-PM1.0-V13-2*40P	2*40	(PIN-1)	(PIN)

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				BXCONN®	
DIM.	TOL.	TITLE: 1.0FH H2.0 2xNPin SMT W2.5 U型 PC3.8 PB2.3 6T					
x.	±0.30						
x.x	±0.20						
x.xx	±0.10						
GENERAL ANGLE:		DWG. NO.: AM-PM1.0-V13-2*NP			CHECKED: MAX		
x.°	±5°	PART NO.: AM-PM1.0-V13-2*NP			DRAWN: ELLA		
x.x°	±1°						
x.xx°	±0.5°						
		UNIT:	SCALE:	SHEET:	DWG. SIZE:	LAYER:	APPROVED: WILL
		mm	none	1 of 1	A4	bxconn	