






NOTES:

1.MATERIAL:

CAGE: COPPER ALLOY,NI PLATING,THICKNESS 0.25mm

MIDDLE CAGE: STAINLESS STEEL

HEAT SINK : ALUMINUM(SURFACE TREATMENT:BLACK OXIDE


HEAT SINK CLIP: STAINLESS STEEL

2.PACKAGING: TRAY PACKAGING

3.TEMPERATURE RANGE:



OPERATING : -40°C TO +85°C

NON OPERATING : -55°C TO +105°C



TITLE SFP+ 1X4 CAGE, WITH HEAT SINK			CND-tek 深圳磁联达电子有限公司 Shen zhen cnd-tek Electronics Co., Ltd			
PART NO. SFP+ 2198241-4 1X4YS-CND			GENERAL TOLERANCE		UNIT:MM	SIZE: A4
APPROVE	CHECK	DRAW	.X±0.20	.X±1°	SCALE: 1:1	SHEET:1/4
QG.CHEN	SL.WANG	X.YAN	.XX±0.15	.XX±5°		
			.XXX±0.10			

RECOMMENDED PCB CONFIGURATION WITH KEEP-OUT AREAS SINGLE SIDED APPLICATIONS





DETAIL H
RECOMMENDED CONNECTOR LAYOUT
4X INDIVIDUALLY

— CROSS-HATCHED AREA DENOTES
COMPONENT AND TRACE KEEP-OUT
(EXCEPT CHASSIS GROUND)

TITLE SFP+ 1X4 CAGE, WITH HEAT SINK			CND-tek 深圳磁联达电子有限公司 Shen zhen cnd-tek Electronics Co., Ltd				
PART NO. SFP+ 2198241-4 1X4YS-CND			GENERAL TOLERANCE			UNIT:MM	SIZE: A4
APPROVE	CHECK	DRAW	.X±0.20	.X±1"	SCALE: 1:1	SHEET:2/4	REV:A
			.XX±0.15	.XX±5"			
QG.CHEN	SL.WANG	X.YAN	.XXX±0.10				



RECOMMENDED PCB CONFIGURATION
WITH KEEP-OUT AREAS
BELLY TO BELLY APPLICATIONS





DETAIL H
RECOMMENDED CONNECTOR LAYOUT
8X INDIVIDUALLY

CROSS-HATCHED AREA DENOTES
COMPONENT AND TRACE KEEP-OUT
(EXCEPT CHASSIS GROUND)

TITLE SFP+ 1X4 CAGE, WITH HEAT SINK			CND-tek 深圳磁联达电子有限公司 Shen zhen cnd-tek Electronics Co., Ltd		
PART NO. SFP+ 2198241-4 1X4YS-CND			GENERAL TOLERANCE		UNIT:MM
APPROVE	CHECK	DRAW	.X±0.20	.X±1"	SCALE: 1:1
QG.CHEN	SL.WANG	X.YAN	.XX±0.15	.XX±5"	SHEET:3/4
			.XXX±0.10		REV:A



RECOMMENDED BEZEL DESIGN
SINGLE SIDED APPLICATIONS



RECOMMENDED BEZEL DESIGN
BELLY TO BELLY APPLICATIONS

TITLE SFP+ 1X4 CAGE, WITH HEAT SINK			CND-tek 深圳磁联达电子有限公司 Shen zhen cnd-tek Electronics Co., Ltd		
PART NO. SFP+ 2198241-4 1X4YS-CND			GENERAL TOLERANCE		UNIT:MM
APPROVE	CHECK	DRAW	.X±0.20	.X±1°	SIZE: A4
QG.CHEN	SL.WANG	X.YAN	.XX±0.15	.XX±5°	SHEET:4/4
			.XXX±0.10		
			SCALE: 1:1		REV:A