





|      |             |   |         |      |      |
|------|-------------|---|---------|------|------|
|      |             | D |         | E    |      |
| REV. | DESCRIPTION |   | ECN NO. | NAME | DATE |
|      |             |   |         |      |      |



**SPECIFICATIONS**  
 Current Rating: 1.0 Amps  
 Withstanding Voltage: AC 500V  
 Insulation Resistance: 1000MΩ Min  
 Contact Resistance: 20mΩ Max  
 Operation Temperature: -40° to +105°  
 Insulator Material: Polyester (UL94V-0)  
 Contact Material: Phosphor bronze  
 Standard: PA6T  
 Contact Plating: Gold Flash  
 Max. Processing Temp: 240°C for 30-60 seconds  
 (260°C for 5 seconds)



RECOMMEND P.C.B LAYOUT

---

PCB TOLERANCE:  $\pm 0.05$  (TOP VIEW)

|                                                                                                         |  |                                                 |                |                  |                  |                                                                                       |                |
|---------------------------------------------------------------------------------------------------------|--|-------------------------------------------------|----------------|------------------|------------------|---------------------------------------------------------------------------------------|----------------|
| GENERAL TOLERANCE                                                                                       |  | DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD   |                |                  |                  | BXCONN <sup>®</sup>                                                                   |                |
| DIM. TOL.<br>x. ±0.30<br>x.x ±0.20<br>x.xx ±0.10<br>GENERAL ANGLE:<br>x° ±5°<br>x.x° ±1°<br>x.xx° ±0.5° |  | TITLE: 1.27FH H4.3 2xNPin SMT U型 PC4.8 PB4.6 6T |                |                  |                  |  |                |
|                                                                                                         |  | DWG. NO.: AM-PM2.54-V13-2*NP                    |                | CHECKED: MAX     |                  |                                                                                       |                |
|                                                                                                         |  | PART NO.: AM-PM2.54-V13-2*NP                    |                | DRAWN: ELLA      |                  |                                                                                       |                |
|                    |  | UNIT:<br>mm                                     | SCALE:<br>none | SHEET:<br>1 of 1 | DWG. SIZE:<br>A4 | LAYER:<br>bxconn                                                                      | APPROVED: WILL |