





ROHS



REV.	ECN NO.	DESCRIPTION	DRAW	DATE

NOTES:

1.ELECTRONIC:

CONTACT CURRENT RATING:1.5A

CONTACT RESISTANCE: 30mohm MAX

INSULATION RESISTANCE: 1000 Mohm MIN

WITHSTAND VOLTAGE:AC 500V,1min.


2.MECHANICAL:

MATING FORCE:3.57KG MAX

UNMATED FORCE:1.02KG MIN

3.ENVIRONMENT CHARACTERISTICS:

OPERTING TEMPERATURE:-25°C TO +85°C



COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD				
DRAWING						
CHECK						
APPROVAL						
TOLERANCES ARE		TITLE	TYPE-A连接器9PIN弯插L16.5(卷口)	REV.	A	
30-150	±0.35	PART NO.	LAIL-TYPE-A-9P-01Y-WC	UNITS	mm	
10-30	±0.2					
5-10	±0.15					
0-5	±0.1					
ANGLE		DWG.NO.		Projection		
±3°						