REV.	DESCRIPTION	ECN NO.	NAME	DATE







Part No	Pin	A	B	C
AF-VH3.96-2PJK-W1	2	3.96	8.20	3.55
AF-VH3.96-3PJK-W1	3	7.92	12.10	7.40
AF-VH3.96-4PJK-W1	4	11.88	16.06	7.40
AF-VH3.96-5PJK-W1	5	15.84	20.02	7.40
AF-VH3.96-6PJK-W1	6	19.80	23.98	7.40
AF-VH3.96-7PJK-W1	7	23.76	27.94	7.40
AF-VH3.96-8PJK-W1	8	27.72	31.90	7.40
AF-VH3.96-9PJK-W1	9	31.68	35.86	7.40
AF-VH3.96-10PJK-W1	10	35.64	39.82	7.40
AF-VH3.96-11PJK-W1	11	39.60	43.78	7.40
AF-VH3.96-12PJK-W1	12	43.56	47.74	7.40

技术要求Specification:

1、材质Material: PA66 UL94V-2(0):

2、额定电流 Current rating:3.0A AC,DC

3、额定电压 Voltage rating:250V AC,DC

4、温度范围 Temperature range:-25℃to+85℃

5、接触电阻 Contact resistance:≤0.02Ω

6、绝缘电阻Insulation resistance:≥1000MΩ

7、耐压Withstand voltage:1000V AC/minute

8、塑件表面平整光洁，无明显的毛刺、气泡、变形、浇口拉伤、缺料等不良现象.

Plastic surface smooth and clean, no obvious glitches, bubbles, distortion, gate strain, lack ofmaterial and other undesirable phenomena.

GENERAL TOLERANCE	DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD		BXCONN®
DIM. TOL. x. ±0.30 x.x ±0.20 x.xx ±0.10 GENERAL ANGLE: x° ±1°	TITLE: VH3.96MM HOUSING		
	DWG. NO.: AF-VH3.96-NPJK-W1	CHECKED: MAX	
	PART NO.: AF-VH3.96-NPJK-W1	DRAWN: ELLA	
	UNIT: mm / SCALE: none / SHEET: 1of 1 / DWG. SIZE: A4 / LAYER: bxconn	APPROVED: WILL	