

# BCH65S30D4

## Silicon Carbide Schottky Diode

650V, 30A



### Description

BCH65S30D4 utilizes Bestirpower’s advanced silicon carbide diode technology. This technology combines the benefits of excellent low forward voltage and robustness. Consequently, the family is suitable for application requiring high power efficiency

### Benefits

- High frequency
- Low heat dissipation requirements
- Reduce size and cost of the system
- High-reliability



### Applications

- Switch mode power supply
- Solar inverter
- Data Center
- Uninterruptible power supply

### Features

| $V_{RRM}$ | $I_F$ | $T_C$  | $Q_c$ |
|-----------|-------|--------|-------|
| 650 V     | 30 A  | 141 °C | 72 nC |

- Negligible reverse recovery
- High-speed switching
- Positive Temperature Coefficient
- Temperature-Independent Switching
- RoHS compliant



### Absolute Maximum Ratings ( $T_C = 25^{\circ}C$ unless otherwise noted)

| Symbol         | Parameter                                  |                                          | Value       | Unit             |
|----------------|--------------------------------------------|------------------------------------------|-------------|------------------|
| $V_{RRM}$      | Repetitive Peak Reverse Voltage            |                                          | 650         | V                |
| $I_F$          | Forward Current                            | $T_C = 25^{\circ}C$                      | 63          | A                |
|                |                                            | $T_C = 135^{\circ}C$                     | 33          | A                |
|                |                                            | $T_C = 141^{\circ}C$                     | 30          | A                |
| $I_{F,SM}$     | Non-Repetitive Forward Surge Current       | $T_C = 25^{\circ}C, t_p = 10\text{ ms}$  | 189         | A                |
|                |                                            | $T_C = 110^{\circ}C, t_p = 10\text{ ms}$ | 126         | A                |
| $I_{F,RM}$     | Repetitive Peak Forward Surge Current      | $T_C = 25^{\circ}C, t_p = 10\text{ ms}$  | 170         | A                |
| $I^2dt$ value  | $\int I^2t$                                | $T_C = 25^{\circ}C, t_p = 10\text{ ms}$  | 179         | A <sup>2</sup> s |
|                |                                            | $T_C = 110^{\circ}C, t_p = 10\text{ ms}$ | 79          | A <sup>2</sup> s |
| $P_{tot}$      | Power Dissipation                          | $T_C = 25^{\circ}C$                      | 292         | W                |
|                |                                            | $T_C = 110^{\circ}C$                     | 126         | W                |
|                |                                            | $T_C = 150^{\circ}C$                     | 49          | W                |
| $T_J, T_{STG}$ | Operating Junction and Storage Temperature |                                          | -55 to +175 | $^{\circ}C$      |

Thermal Characteristics

| Symbol          | Parameter                                  | Value | Unit                        |
|-----------------|--------------------------------------------|-------|-----------------------------|
| $R_{\theta JC}$ | Thermal Resistance, Junction to Case, Typ. | 0.51  | $^{\circ}\text{C}/\text{W}$ |

Electrical Characteristics ( $T_C = 25^{\circ}\text{C}$  unless otherwise noted)

| Symbol   | Parameter                 | Test Conditions                                 | Min | Typ  | Max | Unit          |
|----------|---------------------------|-------------------------------------------------|-----|------|-----|---------------|
| $V_{DC}$ | DC blocking voltage       |                                                 | 650 | -    | -   | V             |
| $V_F$    | Forward Voltage           | $I_F=30\text{A}, T_J=25^{\circ}\text{C}$        | -   | 1.56 | 1.7 | V             |
|          |                           | $I_F=30\text{A}, T_J=175^{\circ}\text{C}$       | -   | 2.2  | -   |               |
| $I_R$    | Reverse Current           | $V_R = 650\text{ V}, T_J = 25^{\circ}\text{C}$  | -   | 0.01 | 5   | $\mu\text{A}$ |
|          |                           | $V_R = 650\text{ V}, T_J = 175^{\circ}\text{C}$ | -   | 1    | -   |               |
| $Q_C$    | Total Capacitive Charge   | $V_R = 400\text{ V}, T_J = 25^{\circ}\text{C}$  | -   | 72   | -   | nC            |
| C        | Total Capacitance         | $V_R = 0\text{ V}, f = 1\text{MHz}$             | -   | 1303 | -   | pF            |
|          |                           | $V_R = 200\text{ V}, f = 1\text{MHz}$           | -   | 136  | -   |               |
|          |                           | $V_R = 400\text{ V}, f = 1\text{MHz}$           | -   | 128  | -   |               |
| $E_C$    | Capacitance Stored Energy | $V_R = 400\text{ V}, T_C = 25^{\circ}\text{C}$  | -   | 17.5 | -   | $\mu\text{J}$ |

Typical Performance Characteristics

Figure 1. Forward Characteristics




Figure 2. Reverse Characteristics




Figure 3. Peak Forward Current Derating




Figure 4. Power Dissipation




Figure 5. Capacitance vs. Reverse Voltage






Figure 6. Capacitance Charge vs. Reverse Voltage





Typical Performance Characteristics

Figure 7. Transient Thermal Impedance



Package Outlines  
TO220-2



**Package Marking and Ordering Information**

| Part Number | Top Marking | Package | Packing Method | Quantity |
|-------------|-------------|---------|----------------|----------|
| BCH65S30D4  | BCH65S30D4  | TO220-2 | Tube           | 50 units |

**Disclaimer**

Bestirpower reserve the right to make changes, corrections, enhancements, modifications, and improvements to Bestirpower products and/or to this document at any time without notice.

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. Bestirpower does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Products or technical information described in this document.

This document is the property of Bestirpower Co., LTD., and not allowed to copy or transformed to other format if not under the authority approval.

© 2026 bestirpower – All rights reserved