

Features

- **Current transfer ratio**
(CTR: 20~300% at $I_F = \pm 1\text{mA}$, $V_{CE} = 5\text{V}$)
- **High isolation voltage between input and output** (Viso = 3750V rms)
- **Collector - emitter breakdown voltage** $BV_{CEO} \geq 80\text{V}$
- **Operating Temperature:** -55°C~100°C


HF

Applications

- Switching power supply, intelligent meter
- Industrial control, measuring instruments
- Office equipment such as copiers
- Household appliances: such as air conditioners, fans, water heaters, etc.

Mechanical Data

- **Case:** SOP4
- **Molding Compound:** UL Flammability Classification Rating 94V-0
- **Terminals:** Matte tin-plated leads; solderability-per MIL-STD-202, Method 208



Ordering Information

TWS 354 (M) (G) (X) - (U) (N) (Y)


① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- ① Brand(TWS)
- ② Product series(354)
- ③ Package type(None:SOP4)
- ④ Halogen option(None :Halogen free)
- ⑤ CTR Bank(A,B or None)
- ⑥ Lead frame (None: Copper)
- ⑦ Customer option 1 (0-9 or A-Z or None)
- ⑧ Customer option 2 (0-9 or A-Z or None)

Part Number	Package	Shipping Quantity	Marking Code
TWS354A	SOP4	3000 pcs / Tape & Reel	TWS354A

Marking Information

- "TWS" denotes brand.
- "354" denotes Product series.
- "X" denotes CTR Rank : A, B , None.
- "Y" denotes Year : A(2024), B(2025), C(2026)
- "WW" denotes Week's number .
- "N" denotes the day of Week.



Maximum Ratings (@ T_A = 25°C unless otherwise specified)

Parameter		Symbol	Value	Unit
Input	Forward Current	I _F	±50	mA
	Power Dissipation	P _D	70	mW
	Power dissipation Derating factor (above T _a = 100°C)	P _{DD}	2.9	mW/°C
	Thermal Resistance Junction-Ambient	R _{thJ-A}	325	°C/W
	Thermal Resistance Junction-Case	R _{thJ-C}	200	°C/W
Output	Power Dissipation	P _C	150	mW
	Collector Current	I _C	50	mA
	Collector-Emitter Voltage	V _{CEO}	80	V
	Emitter-Collector Voltage	V _{ECO}	7	V

Thermal Characteristics

Parameter	Symbol	Value	Unit
Total Power Dissipation	P_{TOT}	200	mW
Isolation Voltage ^{*1}	V_{ISO}	3750	V _{rms}
Operating Temperature	T_{OPR}	-55 ~ +100	°C
Storage Temperature Range	T_{STG}	-55 ~ +125	°C
Soldering Temperature ^{*2}	T_{SOL}	260	°C

Notes:

1. 40 to 60% RH, AC for 1 minute

2. For 10 seconds

Electrical Characteristics (@ $T_A = 25^\circ\text{C}$ unless otherwise specified)

Parameter		Symbol	Test Condition	Min.	Typ.	Max.	Unit
Input	Forward Voltage	V_F	$I_F = \pm 20\text{mA}$	-	1.2	1.4	V
	Terminal Capacitance	C_t	$V = 0, f = 1\text{kHz}$	-	30	250	pF
Output	Collector-Emitter Dark Current	I_{CEO}	$V_{CE} = 20\text{V}, I_F = 0$	-	-	100	nA
	Collector-Emitter Breakdown Voltage	BV_{CEO}	$I_C = 0.1\text{mA}, I_F = 0$	80	-	-	V
	Emitter-Collector Breakdown Voltage	BV_{ECO}	$I_E = 10\mu\text{A}, I_F = 0$	7	-	-	V
Transfer Characteristics	Current Transfer Ratio	CTR	$I_F = \pm 1\text{mA}, V_{CE} = 5\text{V}$	20	-	300	%
	Collector-Emitter Saturation Voltage	$V_{CE(sat)}$	$I_F = \pm 20\text{mA}, I_C = 1\text{mA}$	-	0.1	0.2	V
	Isolation Resistance	R_{ISO}	DC500V, 40~60%R.H	5×10^{10}	1×10^{11}	-	Ω
	Floating Capacitance	C_f	$V = 0, f = 1\text{MHz}$	-	0.6	1.0	pF
	Cut-off Frequency	F_c	$V_{CE} = 5\text{V}, I_C = 2\text{mA}, R_L = 100\Omega, -3\text{dB}$	-	80	-	kHz
	Rise Time	T_r	$V_{CE} = 2\text{V}, R_L = 100\Omega$	-	-	18	μs
	Fall Time	T_f	$I_C = 2\text{mA}$	-	-	18	

Rank Table of Current Transfer Ratio CTR

Rank Mark	Min. (%)	Max. (%)	Condition
A	50	150	$I_F = \pm 1\text{mA}, V_{CE} = 5\text{V}$
B	100	300	
No mark	20	300	

Ratings and Characteristics Curves (@ $T_A = 25^\circ\text{C}$ unless otherwise specified)

Fig.1 Relative Current Transfer Ratio vs Forward Current




Fig.2 Forward Current vs Forward Voltage




Fig.3 Collector Current vs Collector Emitter voltage




Fig.4 Relative Current Transfer Ratio vs Ambient Temperature




Fig.5 Collector-emitter saturation voltage vs. Ambient Temperature




Fig.6 Collector Dark Current vs. Ambient Temperature




Fig.7 Response Time vs. Load Resistance




Fig.8 Frequency Response




Fig.9 Collector-emitter Saturation Voltage vs. Forward Current






Fig.10 Switching Time Test Circuit & Waveforms





Package Outline Dimensions (unit: mm)

SOP4



SOLDERING FOOTPRINT (unit: mm)






	Symbol	Min	Max	Unit
Preheat temperature	Ts	150	200	°C
Preheat time	ts	60	120	s
Ramp-up rate(T _L to T _P)			3	°C/s
Liquidus temperature	T _L	217		°C
Time above T _L	t _L	60	150	s
Peak temperature	T _P		260	°C
Time during which T _c is between (T _P -5) and T _P	t _p		30	s
Ramp-down rate(T _P to T _L)			6	°C/s

Note:

Reflow soldering is recommended at the temperatures and times shown, no more than three times.

Wave soldering



Profile feature	
Average ramp-up rate	~200°C/s
Heating rate during preheat	1°C/s to 2°C/s typical; 4°C/s maximum
Final preheat temperature Ts	~130°C
Preheat time (25°C to Ts)	> 60s
Peak temperature Tp	260°C
Time within peak temperature tp	10s
Ramp-down rate	5°C/s maximum

Soldering with hand soldering iron

- Hand soldering iron is only used for product rework or sample testing.
- Hand soldering iron requirements: Temperature: 360 °C±5°C within 3s.

Packing

Package Type	Packing Form	Quantity per Tube &Reel	Quantity per Box	Quantity per Carton	Antistatic Bag Specification	Box Specification	Carton Specification	Note
SOP4	Reel($\phi 330$ mm)	3000 pcs/reel	2 reels /box	5 boxes /ctn	380*420mm	350*340*60mm	365*330*370mm	Leave 20 Spaces at the beginning and 50 Spaces at the end


■Summary table

■SOP4 (Reel)

Qty/reel: 3000 pcs. Qty/box: 6000 pcs.

Qty/ctn : 30000 pcs.

Schematic: (unit:mm)



IMPORTANT NOTICE

TAIWEI semiconductor reserves the right to make changes without further notice to any product herein to make corrections, modifications, improvements, or other changes. TAIWEI semiconductor does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights ,nor the rights of others .