




NOTES

MATERIAL
1.HOUSING MATERIAL : PBT BLACK UL94V-0.
2.CONTACT MATERIAL : PHOSPHOR BRONZE $\phi 0.46\text{mm}$.
3.PLATING : GOLD FLASH PLATING .
4.SHELL: : BRASS T=0.2mm NI PLATING.
ELECTRICAL
1.VOLTAGE RATING : 125 VAC RMS.
2.CURRENT RATING : 1.5 AMP.
3.CONTACT RESISTANCE : 40 MILLIOHMS MAX.
4.INSULATION RESISTANCE : 500 MEGOHMS MIN @ 100V DC .
5.DIELECTRIC DIELECTRIC RESISTANCE : 500V DC RMS 50Hz. 1MIN.

MECHANICAL
1.DURRABILITY : 750 CYCLES MIN.
2. MATING/UNMATING FORCE : 2.24 KG.F MAX.

ENVIRONMENTAL:
1.STORAGE : $-40^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
2.OPERATION : $-40^{\circ}\text{C}\sim+85^{\circ}\text{C}$.



RECOMMEND PCB LAYOUT (TOP View)

T=1.60MM TOLERANCE: $\pm 0.05\text{MM}$

PART NUMBER DESCRIPTION:

RJ45-401-043-XX

流水码 
11:B3.85 GF PBT黑盘装

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: RJ45 52立式有壳无灯B3.85 DIP
			PAR RJ45-403-043-11
DECIMALS:	ANGLES:		DWN
X.X ± 0.20	X. $^{\circ}\pm 5^{\circ}$		CHKD
X.XX ± 0.15	X.X $^{\circ}\pm 2^{\circ}$	CUSTOMER COPY	APVD
X.XXX ± 0.05	X.XX $^{\circ}\pm 1^{\circ}$		SCALE N:A UNIT:MM
		SIZE:A4	SHEET:1F1
			REV:A