


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	1	DRAFT RELEASE	02MAR2021	E.Z	J.Z
	A	RELEASED	16MAY2022	C.C	J.Z
	A1	REVISED ECR-23-167327	22FEB2023	C.C	J.Z



- 1 2386381-1 AS LEFT SHOWN
- 2 BULK PACKAGING
- 3 TE PART NUMBER
- 4 CAVITY 1~6 APPLICABLE FOR MCP 2.8
CAVITY 7~36 APPLICABLE FOR MQS 0.64
SUITABLE TERMINALS SEE TABLE
- 5 SUITABLE COVER ASSY 2386378
- 6 INTERFACE DRAWING 114-160105

MQS 0.64	5-963715-1	0.5-0.75	1.4-1.9	114-18021	PRE-TIN	929454
	5-928999-1	0.25-0.35	1.1-1.4			
	1355717-1	0.22	1.1-1.2			
MCP 2.8	1-968853-1	4.0	3.4-3.7	114-18148	PRE-TIN	1355036
	1-968851-1	1.5-2.5	2.2-3.0			
	1-968849-1	0.5-1.0	1.4-2.1			
	1-2141857-1	0.2-0.5	1.2-1.4			
TERMINAL	TE PART NO	WIRE SIZE (mm ²)	INSULATION RANGE REF (mm)	APPLICATION SPEC	SURFACE TREATMENT	GROUP DRAW ING

AI	2386381-2	32P SOCKET HOUSING	PBT-GF20	BLACK
	2386381-1	36P SOCKET HOUSING		
	TE PN	DESCRIPTION	MATERIAL	COLOR

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E.ZOU	26FEB2021	TE Connectivity		
		CHK G.ZHU	26FEB2021			
		APVD J.ZONG	26FEB2021	NAME REC SOCKET HOUSING 36POS HYBRID 6xMCP 2.8 + 30xMQS 0.64		
		PRODUCT SPEC	108-160219			
		APPLICATION SPEC	-	SIZE	CAGE CODE	DRAWING NO
		WEIGHT	-	A2	00779	C=2386381
		CUSTOMER DRAW ING	SCALE	2:1	SHEET	1 OF 1
						REV A1

D

C

B

A

D

C

B

A

