

General Description

The CMH50N50 have been fabricated using an advanced high voltage MOSFET process that is designed to deliver high levels of performance and robustness in popular AC-DC applications. These parts can be adopted quickly into new and existing offline power supply designs.

Features

- Low gate input resistance
- 100% avalanche tested
- RoHS Compliant

Product Summary

BVDSS	R _{DS(on)} max.	ID
500V	0.105Ω	50A

Applications

- Switching applications

TO-247 Pin Configuration



Type	Package	Marking
CMH50N50	TO-247	CMH50N50

Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V _{DS}	Drain-Source Voltage	500	V
V _{GS}	Gate-Source Voltage	±30	V
I _D @T _C =25°C	Continuous Drain Current	50	A
I _D @T _C =100°C	Continuous Drain Current	40	A
I _{DM}	Pulsed Drain Current	200	A
EAS	Single Pulse Avalanche Energy ¹	4205	mJ
P _D @T _C =25°C	Total Power Dissipation	625	W
T _{STG}	Storage Temperature Range	-55 to 150	°C
T _J	Operating Junction Temperature Range	-55 to 150	°C

Thermal Data

Symbol	Parameter	Rating	Unit
R _{θJA}	Thermal Resistance Junction-ambient	40	°C/W
R _{θJC}	Thermal Resistance Junction-case	0.2	°C/W

Electrical Characteristics ($T_J=25^{\circ}\text{C}$, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS}=0V, I_D=250\mu A$	500	---	---	V
$R_{DS(ON)}$	Static Drain-Source On-Resistance	$V_{GS}=10V, I_D=25A$	---	---	0.105	Ω
$V_{GS(th)}$	Gate Threshold Voltage	$V_{GS}=V_{DS}, I_D=250\mu A$	2	---	4	V
I_{DSS}	Drain-Source Leakage Current	$V_{DS}=500V, V_{GS}=0V$	---	---	1	μA
I_{GSS}	Gate-Source Leakage Current	$V_{GS}=\pm 30V, V_{DS}=0V$	---	---	± 100	nA
g_{fs}	Forward Transconductance	$V_{DS}=25V, I_D=25A$	---	50	---	S
Q_g	Total Gate Charge	$I_D=23A$	---	180	---	nC
Q_{gs}	Gate-Source Charge	$V_{DS}=400V$	---	39	---	
Q_{gd}	Gate-Drain Charge	$V_{GS}=10V$ (note 2,3)	---	57	---	
$T_{d(on)}$	Turn-On Delay Time	$V_{DD}=250V$	---	62	---	ns
T_r	Rise Time	$I_D=23A$	---	24	---	
$T_{d(off)}$	Turn-Off Delay Time	$R_G=25\Omega$ (note 2,3)	---	188	---	
T_f	Fall Time		---	23	---	
C_{iss}	Input Capacitance	$V_{DS}=25V, V_{GS}=0V, f=1\text{MHz}$	---	9500	---	pF
C_{oss}	Output Capacitance		---	700	---	
C_{rss}	Reverse Transfer Capacitance		---	70	---	

Diode Characteristics







Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I_S	Continuous Source Current	$V_G=V_D=0V, \text{Force Current}$	---	---	50	A
I_{SM}	Pulsed Source Current		---	---	200	A
V_{SD}	Diode Forward Voltage	$V_{GS}=0V, I_S=48A$	---	0.89	1.5	V
t_{rr}	Reverse Recovery Time	$I_S=50A, V_{GS}=0V$	---	487	---	ns
Q_{rr}	Reverse Recovery Charge	$di/dt=100A/\mu s$ (note 2,3)	---	6.9	---	μC

Note :



1. The EAS data shows Max. rating .The test condition is $V_{DS}=100V, V_{GS}=10V, L=10mH, I_{AS}=29A$.
2. Pulse test: Pulse width $\leq 300\mu s$, Duty cycle $\leq 2\%$.
3. Essentially independent of operating temperature typical characteristics.

This product has been designed and qualified for the consumer market.
 Cmos assumes no liability for customers' product design or applications.
 Cmos reserves the right to improve product design ,functions and reliability without notice.Please refer to the latest version of specification.

Typical Characteristics




Typical Characteristics



Package Dimension

TO-247

Unit :mm



符号	机械尺寸/mm			符号	机械尺寸/mm		
	最小值	典型值	最大值		最小值	典型值	最大值
A	4.80	5.00	5.20	E2		5.00	
A1	2.21	2.41	2.61	E3		2.50	
A2	1.90	2.00	2.10	e		5.44	
b	1.10	1.20	1.35	L	19.42	19.92	20.42
b1		2.00		L1		4.13	
b2		3.00		P	3.50	3.60	3.70
c	0.55	0.60	0.75	P1		7.19	
D	20.80	21.00	21.20	P2		2.50	
D1		16.55		Q		5.80	
D2		1.20		S	6.05	6.15	6.25
E	15.60	15.80	16.0	T		10.00	
E1		13.30		U		6.20	