


修 订	标 记	修 改 描 要	签 名	日 期
REV A0		NEW DWG		2016-03-12



NOTES:

- 1.HUOSING: LCP HIGH-TEMP THERMOPLASTIC UL94V-0 COLOR:NATURE
- 2.ACTUATOR: LCP HIGH-TEMP THERMOPLASTIC UL94V-0 COLOR:BLACK
- 3.TERMINAL:PHOSPHOR BRONZE

PLATING:1* μ "GOLD FLASH OR 100~150* μ "TIN(LEAD FREE)
OVERALL 50~100* μ "NICKEL UNDER PLATED.

- 4.FITTING NAIL:PHOSPHOR BRONZE

PLATING:100~150* μ "TIN(LEAD FREE)
OVERALL 50~100* μ "NICKEL UNDER PLATED.

- 5.SPECIFICATION:




CURRENT RATING: 0.5A 50V AC/DC

CONTACT RESISTANCE: 30m Ω MAX


INSULATION RESISTANCE: 100M Ω AT 500V DC

OPERATING TEMPERATURE RANGE: -40°C~85°C


WITHSTANDING VOLTANG: 500V AC/minute




CABLE INSERT DIM.
SCALE 2:1



COVER OPEN DIM.
SCALE 2:1



3D VIEW



RECOMMENDED PCB PATTERN DIM.

TOLERANCE : ± 0.05

NO.of contacts	Dimensions				
	A.	B.	C.	D.	E.
60	37.00	29.50	37.24	34.10	32.60
68	41.00	33.50	41.24	38.10	36.60
80	47.00	39.50	47.24	44.10	42.60
96	55.00	47.50	55.24	52.10	50.60




深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co.,LTD

电话：0755-27111216 传真：0755-29940187


-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表		TITLE: 产品名称: FPC0.5间距2.1高掀盖下接带扣	
X.X ± 0.30	X.X* $\pm 3^{\circ}$	APPD: 核准:	PART NO: 产品编号: HDGC0524-xxCL-GF
X.XX ± 0.20	X.XX* $\pm 2^{\circ}$	CHECK: 校对: 王建业	DATE
X.XXX ± 0.10	X.XXX* $\pm 1^{\circ}$	DRAW: 绘图: 黄艳兰	SCALE
			UNIT
			CODE NUMBER
		2016-03-12	1:1
			mm
			A001

修 订 REV NO	标 记 MARK	修 改 描 要 REVISION DESCRIPTION	签 名 SIGNATURE	日 期 DATE
		NEW DWG		2016-03-12



APPLICABLE FPC/FFC

蓝白裸线（不接地）



APPLICABLE FPC/FFC

一体补强板铝箔FFC线

NO.of contacts	Dimensions			
	B.	E.	F.	G.
60	29.50	34.05	35.00	32.55
68	33.50	38.05	39.00	36.55
80	39.50	44.05	45.00	42.55
96	47.50	52.05	53.00	50.55

一体补强板铝箔FFC线



深圳市华德共创科技有限公司
Shenzhen Huade co-create Technology Co.,LTD
电话：0755-27111216 传真：0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表			TITLE: 产品名称: FPC0.5间距2.1高掀盖下接带扣			
X.X	±0.30	X.X*	±3°	PART NO: 产品编号: HDGC0524-xxCL-GF		
X.XX	±0.20	X.XX*	±2°	CHECK: 核准: 王建业	DATE	SCALE
X.XXX	±0.10	X.XXX*	±1°	DRAW: 绘图: 黄艳兰	UNIT	CODE NUMBER
				2016-03-12	1:1	mm
						A001

A

B







C

D

E

F

修 订	标 记	修 改 描 要	签 名	日 期
REV A0		NEW DWG		2016-03-12



NOTES:

- 1.Component load per 13" reel:2000 pcs
- 2.Material: white conductive polystyrene alloy.
- 3.Thickness:0.3±0.05mm
- 4.All dimensions meet EIA-481-C requirements



深圳市华德共创科技有限公司
Shenzhen Huade co-create Technology Co., LTD
电话：0755-27111216 传真：0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表		TITLE: 产品名称: FPC0.5间距2.1高掀盖下接带扣	
X.X ±0.30	X.X* ±3°	APPD: 核准:	PART NO: 产品编号: HDGC0524-xxCL-GF
X.XX ±0.20	X.XX* ±2°	CHECK: 校对: 王建业	DATE SCALE UNIT CODE NUMBER
X.XXX ±0.10	X.XXX* ±1°	DRAW: 绘图: 黄艳兰	2016-03-12 1:1 mm A001