

A

B





C

D

E

F

修订	标记	修改摘要	签名	日期
REV	MARK	REVISION DESCRIPTION	SIGNATURE	DATE
AO		NEW DWG		2016-03-12



SPECIFICATION

1. Electrical characteristics

Contact Current Rating: 0.5 A

Dielectric Withstanding Voltage: 300V AC

Insulation Resistance: a. Mate 100M Ω MIN at 500V/DCb. Unmate 10M Ω MIN at 150V/DCContact Resistance: 30m Ω MAX

Temperature Range: -20° C to +85° C

2. Mechanical

Mating Face: 44.1N MAX

Unmating Face: 9.8N MIN; 39.2N MAX

Durability: 5000 Cycles

3. Material:

HOUSING: THERMOPLASTICS HIGH TEMP LCP+GLASS

FIBER BLACK COLOR, UL94V-0

CONTACT: Copper Alloy, T=0.20MM

SHELL: Copper Alloy (SPCC), T=0.50MM

4. PLATING:

CONTACT: 1~30u" GOLD/TIN PLATING ON CONTACT AREA

100u" MIN, TIN PLATING ON SOLDER TAILS

50u" MIN, NICKEL UNDERPLATING OVER ALL


SHELL: 80u", NICKEL UNDERPLATING OVER ALL



深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co., LTD

电话: 0755-27111216 传真: 0755-29940187

-TOLERANCES-
UNLESS OTHERWISE SPECIFIED
公差参数表TITLE: HDMI AF夹板 1.2铜壳 0.5镀镍
产品名称: 黑胶弯端X.X ± 0.30 X.X* $\pm 3^\circ$ APPD:
核准:PART NO:
产品编号: HDMI-GD-127PWBX.XX ± 0.20 X.XX* $\pm 2^\circ$ CHECK:
校对:

王建业

DATE

SCALE

UNIT

CODE NUMBER

X.XXX ± 0.10 X.XXX* $\pm 1^\circ$ DRAW:
绘图:

黄艳兰

2016-03-12

1:1

mm

A001