




Parameter Specification Details
Thread Specification: 4-40 UNC
(American coarse thread, pitch 0.635mm, major diameter $\approx$ 2.84mm)
Overall Total Length: L40mm
(Customizable lengths including 38/42/47/50mm)
Plastic Handle Outer Diameter: A8mm
(Knurled anti-slip design, equipped with slotted/cross recess)
Plastic Handle Length: H16mm
(Black ABS injection molding, insulated and scratch-resistant)
Metal Rod Diameter: D2.3mm
(Nickel-plated/zinc-plated carbon steel, rust-proof and wear-resistant)
Effective Thread Length: F24mm
(Compatible with standard equipment screw hole depth)
Middle Smooth Rod Section: Optional (Transition section diameter B=4mm, serving as limit and positioning)
End Recess Type: Exposed slotted/cross recess (Compatible with screwdriver use and manual twisting)

Unless otherwise specified tolerance
X. ± 0.25 X.XX: ± 0.10
X.X: ± 0.15 ANGULAR $\pm 3^\circ$

SCALE: As Shown UNIT: mm
DRAW DATE
CHECK DATE
VER A0 3rd ANGLE PROJECTION



安泰珂电子有限公司
Antenk Electronics Co., Ltd

TITLE: 4.0*40mm电脑注塑螺丝

DRAWING NO: 1.03.00600050

PRODUCT NO:

REV	DESCRIPTION	DATE