


**Features**


- Super Low Gate Charge
- 100% EAS Guaranteed
- Green Device Available
- Excellent CdV/dt effect decline
- Advanced high cell density Trench technology

Bvdss**30V****Rdson****20mΩ****ID****9.5A****Application****RoHS**


- Power management in half bridge and inverters
- Load Switch
- DC-DC Converter

Package

Marking and pin assignment



SOP-8 top view



Schematic diagram

Package Marking and Ordering Information

Device Marking	Device	Device Package	Quantity
4822	HL4822A	SOP-8	3000

Absolute Maximum Ratings

Parameter	Symbol	Value	Unit
Drain-Source Voltage	V_{DS}	30	V
Gate-Source Voltage	V_{GS}	± 20	V
Continuous Drain Current, $V_{GS}@10V^1$	$I_D@T_A=25^\circ C$	9.5	A
	$I_D@T_A=70^\circ C$	5.8	A
Pulsed Drain Current ²	I_{DM}	37	A
Single Pulsed Avalanche Energy ³	E_{AS}	12.1	mJ
Avalanche Current	I_{AS}	--	A
Total Power Dissipation ⁴	$P_D@T_A=25^\circ C$	2.8	W
Operating Junction Temperature Range	T_J	-55 ~ 150	$^\circ C$
Storage Temperature Range	T_{STG}	-55 ~ 150	$^\circ C$

Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
$R_{\theta JA}$	Thermal Resistance Junction-Ambient ¹	--	--	$^\circ C/W$
$R_{\theta JC}$	Thermal Resistance Junction-Case ¹	--	46	$^\circ C/W$



Ordering Information

Ordering Number	Package	Pin Assignment			Packing
Halogen Free		G	D	S	
HL4822A	SOP-8	2,4	5,6,7,8	1,3	Tape Reel

Electrical Characteristics ($T_J=25^{\circ}\text{C}$ unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Units
Drain-Source Breakdown Voltage	$V_{(BR)DSS}$	$V_{GS}=0V$, $I_D=-250\mu A$	30	-	-	V
Zero Gate Voltage Drain Current	I_{DSS}	$V_{DS}=30V$, $V_{GS}=0V$	-	-	1	μA
Gate to Body Leakage Current	I_{GSS}	$V_{DS}=0V$, $V_{GS}=\pm 20V$	-	-	± 100	nA
Gate Threshold Voltage	$V_{GS(th)}$	$V_{GS}=V_{DS}$, $I_D=250\mu A$	1	1.5	2.5	V
Static Drain-Source On-Resistance ³	$R_{DS(on)}$	$V_{GS}=10V$, $I_D=5A$	-	20	26	m Ω
		$V_{GS}=4.5V$, $I_D=3A$	-	24	31	
Input Capacitance	C_{iss}	$V_{DS}=15V$, $V_{GS}=0V$, $f=1MHz$	-	490	-	pF
Output Capacitance	C_{oss}		-	79	-	
Reverse Transfer Capacitance	C_{rss}		-	61	-	
Total Gate Charge	Q_g	$V_{DS}=15V$, $V_{GS}=10V$, $I_D=5.8A$	-	10	-	nC
Gate-Source Charge	Q_{gs}		-	1.7	-	
Gate-Drain("Miller")Charge	Q_{gd}		-	2.5	-	
Turn-on Delay Time	$T_{d(on)}$	$V_{DS}=15V$, $I_D=3A$, $V_{GS}=10V$, $R_{GEN}=3\Omega$	-	6	-	ns
Turn-on Rise Time	T_r		-	15	-	
Turn-off Delay Time	$T_{d(off)}$		-	17	-	
Turn-off Fall Time	T_f		-	17	-	
Maximum Continuous Drain to Source Diode Forward Current	I_S	--	-	-	9	A
Maximum Pulsed Drain to Source Diode Forward Current	I_{SM}	--	-	-	36	A
Drain to Source Diode Forward Voltage	V_{SD}	$I_S=9A$, $V_{GS}=0V$	-	-	1.2	V
Body Diode Reverse Recovery Time	t_{rr}	$I_F=5A$, $dI/dt=100A/\mu s$	-	7	-	ns
Body Diode Reverse Recovery Charge	Q_{rr}		-	2	-	nC

Notes:

1. Repetitive Rating: Pulse Width Limited by Maximum Junction Temperature
2. EAS condition : $T_J=25^{\circ}\text{C}$, $V_{DD}=15V$, $V_G=10V$, $L=0.5mH$, $R_g=25\Omega$, $I_{AS}=6A$
3. Pulse Test: Pulse Width $\leq 300\mu s$, Duty Cycle $\leq 0.5\%$



Typical Performance Characteristics

Figure1: Output Characteristics




Figure 2: Typical Transfer Characteristics




Figure 3: On-resistance vs. Drain Current




Figure 4: Body Diode Characteristics




Figure 5: Gate Charge Characteristics











Figure 6: Capacitance Characteristics



**Figure 7:** Normalized Breakdown Voltage vs. Junction Temperature**Figure 8:** Normalized on Resistance vs. Junction Temperature**Figure 9:** Maximum Safe Operating Area**Figure 10:** Maximum Continuous Drain Current vs. Ambient Temperature**Figure.11:** Maximum Effective Transient Thermal Impedance, Junction-to-Ambient



Package Mechanical Data SOP-8



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	1.350	1.750	0.053	0.069
A1	0.100	0.250	0.004	0.010
A2	1.350	1.550	0.053	0.061
b	0.330	0.510	0.013	0.020
c	0.170	0.250	0.006	0.010
D	4.700	5.100	0.185	0.200
E	3.800	4.000	0.150	0.157
E1	5.800	6.200	0.228	0.244
e	1.270(BSC)		0.050(BSC)	
L	0.400	1.270	0.016	0.050
θ	0°	8°	0°	8°



Important Notice and Disclaimer

HL Microelectronics reserves the right to make changes to this document and its products and specifications at any time without notice.

Customers should obtain and confirm the latest product information and specifications before final design, purchase or use.

HL Microelectronics makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, not does HL Microelectronics assume any liability for application assistance or customer product design.

HL Microelectronics does not warrant or accept any liability with products which are purchased or used for any unintended or unauthorized application.

No license is granted by implication or otherwise under any intellectual property rights of HL Microelectronics.

HL Microelectronics products are not authorized for use as critical components in life support devices or systems without express written approval of HL Microelectronics.