



P.C.B LAYOUT

Poles	PART NO.	Dimension mm	
		A	B
2*1	W-5557S02P-B000	/	5.60
2*2	W-5557S04P-B000	4.20	9.80
2*3	W-5557S06P-B000	8.40	14.00
2*4	W-5557S08P-B000	12.60	18.20
2*5	W-5557S10P-B000	16.80	22.40
2*6	W-5557S12P-B000	21.00	26.60
2*7	W-5557S14P-B000	25.20	30.80
2*8	W-5557S16P-B000	29.40	35.00
2*9	W-5557S18P-B000	33.60	39.20
2*10	W-5557S20P-B000	37.80	43.40
2*11	W-5557S22P-B000	42.00	47.60
2*12	W-5557S24P-B000	46.20	51.80

TOLERANCE TABLE

.0	±0.30
.00	±0.15
.000	±0.05

SPECIFICATION

Voltage rating:AC,DC 300V

Current rating:AC,DC,7A

Withstand voltage:1500V AC min.

Insulation resistance:1000M Ω min.

Temperature range:-25℃~+85℃

Applicable PC board thickness:0.031"~0.063"
(0.8~1.6mm)

Contact resistance:Initial value 10m Ω max.


After environmental testing 20m Ω max.

Material:PA66 UL94V-0(2)

Contact:Brass

Finish:Tin-plated

Color:White



APPROVED:	DATE:	Ckmtw 深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRY CO., LTD			
CHECKED:	DATE:	TITLE: 5557S-2*XP 直针 方针 白色			
DRAWN: LYF	DATE: 2024-04-07	PRAT. NO.		W-5557SXXP-B000	
		UNIT	mm	SCALE	free
		FILE NO.	Ckmtw-5557-0033	REV.	A ZW00