

修订 REV	标记 MARK	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE
A0		NEW RELEASE	黄艳兰	2020-09-18

Specifications:

Contact resistance:≤20mΩ

Insulation resistance:≥500MΩ

Rated voltage:100V AC DC

Rated current:2.0A AC DC(AWG#24)

Withstand Voltage: 500V AC/minute

Temperature Range:−40℃~ +105℃

Housing:LCP UL94V−0,Natural(Beige)

Contacts:Phosphor Bronze/Sn−plated

Solder Tabs:Brass/Sn−plated

尺寸	尺寸	尺寸	尺寸	尺寸	尺寸	尺寸	尺寸
孔位	A	B	C	孔位	A	B	C
2P	7.30	1.50	4.45	9P	17.80	12.00	14.95
3P	8.80	3.00	5.95	10P	19.30	13.50	16.45
4P	10.3	4.50	7.45	11P	20.80	15.00	17.95
5P	11.8	6.00	8.95	12P	22.30	16.50	19.45
6P	13.3	7.50	10.45	13P	23.80	18.00	20.95
7P	14.80	9.00	11.95	14P	25.30	19.50	22.45
8P	16.30	10.50	13.45	15P	26.80	21.00	23.95




深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co.,LTD

电话：0755-27111216 传真：0755-29940187

-TOLERANCES-
UNLESS OTHERWISE SPECIFIED
公差参数表



TITLE:
产品名称：1.5卧贴

X.X ±0.30 X.X° ±3°

APPD:
核准：谢亮

PART NO:
产品编号：HDGC1501WRA-S-XP

X.XX ±0.30 X.XX° ±2°








CHECK:
校对：王建业

DATE SCALE UNIT CODE NUMBER

X.XXX ±0.10 X.XXX° ±1°

DRAW:
绘图：黄艳兰

2020-09-18 1:1 mm A018



PCB LAYOUT

Circuits	DIM. D	DIM. E	Q'ty/Reel	Packing (Reel/Caton)
02~03 PIN	7.5	16	800PCS	20/Reel
04~07 PIN	11.5	24	800PCS	15/Reel
08~11 PIN	14.2	32	800PCS	11/Reel
12~15 PIN	20.2	44	800PCS	8/Reel