






RoHS



PCB Layout(Pattern side)



Circuit Diagram



TOTAL HEIGHT	
Code	H
025	2.5
027	2.7
031	3.1
034	3.4
037	3.7
043	4.3
050	5.0
055	5.5

Product No. : TS-080W-□-□-□

型号:

产品高度 (H) :

025=2.5mm

027=2.7mm

031=3.1mm

: 包装方式

-P=编带(非编带, 不启用)

: 弹片

D2=SUS/1PCS

操作力度:

120=120gf±50gf

180=180gf±50gf

250=250gf±50gf

(E)	Terminal		4	Brass	Silvering
(D)	Contact		1	SUS	Silver covered
(C)	Base		1	PPA	Black
(B)	Cover		1	Brass	Plating Cu Sn
(A)	Knob		1	PPA	
NO.	Name	Number	Qty	Materil	Remarks

ZHONGDI®

Zhongdi Electronic Technology Co., Ltd

design
Review
Approved

date
date
date

name

TACT SWITCHS

model

TS-080W-□-□-□

Drawing number:

Proportion 1:1 unit mm gage number A4

modify Review Approved

angle ±2°
10~30 ±0.30
5~10 ±0.20
~ 5 ±0.10

Tolerance not specified

项 目 Item	技术参数 Technical Parameter	标 准 Standard
电气性能 Electrical Properties	额定电流 Rated Current:	50mA
	额定电压 Rated voltage:	DC 12V
	接触电阻 Contact resistance:	≤100mΩ
	绝缘电阻 Insulation Resistance:	DC 250V 1 min ≥100MΩ
机械性能 Mechanical Properties	耐压强度 Compressive strength:	AC 250V 50Hz/1 min
	机械寿命 Mechanical life:	200,000 cycles Min
环境性能 Environmental	操作行程 Operation Stroke:	0.25±0.10mm
	工作温度 Operation temperature:	-25℃~ +75℃
可靠性特性 Reliability Characteristics	使用湿度 Use humidity:	≤85% RH
	回流焊 Reflow Soldering:	≤260℃ 时间 Time 3s
	波峰焊 Wave soldering:	
应用领域 Application area	手工焊 Manual welding:	≥260℃ 时间 Time 3s
	影音产品、电子玩具、数码产品、通讯产品、安防产品等. Audiovisual products, electronic toys, digital products, communication products, security products, etc	



绝缘电阻测量仪




直流低电阻测试仪




耐电压测试仪



回流焊机



二次元测量仪



高精密寿命测试仪



盐雾测试仪



按键荷重曲线仪

ZHONGDI® 众迪										Zhongdi Electronic Technology Co., Ltd													
design			date			name			TACT SWITCHS														
Review			date																				
Approved			date			model			TS-080W-□□-D□														
number:																							
1:1		unit		mm		gape		number												A4			